



Gardall's New Two-Hour Safes, with the Most Features in the Industry

MODELS
1812-3018
ARE NOW
**UL-BF
SAFES**

Can Your Business or Home Office Survive Record Losses From Fire?

Statistics show that if a company's records are lost in a fire, 17% can no longer furnish a financial statement, 14% suffer a reduction in credit rating and 43% go out of business completely. No home or business is safe from fire. Your vital records and possessions are only as safe as the quality of protection you provide for them. With Gardall fire resistive safes, you can be confident your records will survive.



Standard Features

- Thick 4¼" door with recessed anti-pry design. Safe walls are 2½" thick
- Five active bolts that lock in 3 directions, massive 1" diameter round bolts that extend deep into safes' body (Models 1812-3018)
- Center bolt down hole with hardware included for easy installation (hardware included)
- Plush carpeted quality interior to protect valuables
- UL listed, S&G Group II combination lock
- UL 2-Hour Fire Label, furnace-tested to 1850°F for 2 hours. Interior temperature of safe was less than 350°F during the test and cool down
- UL-RSC Burglary Label Models 1812/2 – 3018/2

- Solid chrome-plated handle with shear point to prevent the safe from being forced open by handle attack
- Independent re-locker and hardplate to prevent drilling attack on locking mechanism
- **Gardall Lifetime Replacement Warranty** (see inside front cover)

Options

- Key locking dial
- Push button electronic lock
- Custom Paint with Gold trim – rich color exteriors (Black, Burgundy, or Hunter Green)

Standard colors: Sandstone or Gray.



Model	Outside Dimensions			Inside Dimensions			Cubic Inches	Weight (lbs.)	Shelves
	H	W	D	H	W	D			
1612/2*	23¼"	17¼"	19¾"	16"	12"	11¾"	2256	298	1
1812/2	25"	17¼"	19¾"	18"	12"	11¾"	2538	313	1
1818/2	25"	17¼"	25¾"	18"	12"	17¾"	3834	392	1
171718/2	25"	23¼"	25¾"	18"	18"	17¾"	5751	487	2
2218/2	29¼"	23¼"	25¾"	22"	18"	17¾"	7029	525	2
3018/2	37¼"	23¼"	25¾"	30"	18"	17¾"	9585	620	3

Add 2" to outside depth for dial and handle. *Not available with UL-RSC Label.

All specifications are subject to change without notice. The above mentioned Gardall fire resistive safes carry a U.L. 2 hour 350° Fire Label as to Fire and Impact tests.

Visit us online at www.gardall.com