

VON DUPRIN。 98/99™ Series Exit devices

Introduction

Exit devices are a critical part of the fire and life safety egress system and will provide safe and reliable service when properly applied and maintained. Von Duprin designs and manufactures exit devices in accordance to ISO 9001 Quality Management System and meets or exceeds accepted U.S. domestic and International standards. All 98 and 99 Series exit devices are UL listed for panic hardware or fire hardware, and are certified to ANSI A156.3, 2008, Grade 1. Many models are also certified for Hurricane Resistant Applications. Consult your local Security & Safety consultant (SSC) or the Von Duprin factory for current listings.

It is intended that the information included in this publication, when properly used, will provide clear and reliable guidelines to the proper general selection and application. However, the scope of the information is necessarily limited.



Von Duprin exit devices are available in two external surface styles, designated 98 and 99 Series.



The Quiet One® A fluid damper decelerates the pushpad on its return stroke and eliminates most noise associated with exit device operations. Furnished on all 98/99[™] Series exit devices.





Latch bolt Deadlocking latchbolt provides security and improved performance at standard device cost.

VON DUPRIN

Administrative Offices 2720 Tobey Dr. Indianapolis, IN 46219 **Customer Service** 877-671-7011 800-999-0328 - Fax Technical Support 877-671-7011

Table of contents

Exit hardware		👋 Fire exit
Rim devices		Rim device
98/99	8	98-F/99-F
Trim	9	Trim
XP rim devices		XP rim dev
XP98/99	12	XP98/99-F
Trim	13	Trim
Mortise lock devices		Mortise loo
9875/9975	16	9875/9975
Trim	17	Trim
Surface mounted Vertical rod devices		Surface m Vertical ro
9827/9927	20	9827-F/99
Trim	21	Trim
Three-point latching devic	ces	Three-poir
9857/9957	24	9857-F/99
Trim	25	Trim
Concealed vertical rod devices		Concealed rod device
9847/9947	28	9847-F/99
Trim	29	Trim
9848/9948	32	9848-F/99
Trim	33	Trim
Concealed vertical cable devices		Concealed cable devi
9849/9949	36	9849-F/99
Trim	37	Trim
Wood door concealed vertical rod devices		Wood door vertical roo
9847WDC/9947WDC	40	9847WDC-
Trim	41	Trim
Wood door concealed		Wood door
THIS PRODUCT IS C	DBSOLETE if ee pages 48-51 f	t is replaced by or more informatio
Trim	45	Trim
Wood door concealed vertical cable devices		Wood door vertical ca
9850WDC/9950WDC	48	9850WDC-
Trim	49	Trim

á	
Fire exit hardware	
	10
98-F/99-F Trim	10 11
XP rim devices	
XP98/99-F	14
Trim	15
Mortise lock devices	
9875/9975	18
Trim	19
Surface mounted Vertical rod devices	
9827-F/9927-F	22
Trim	23
Three-point latching devices	
9857-F/9957-F	26
Trim	27
Concealed vertical rod devices	
9847-F/9947-F	30
Trim	31
9848-F/9948-F	34
Trim	35
Concealed vertical cable devices	
9849-F/9949-F	38
Trim	39
Wood door concealed vertical rod devices	
9847WDC-F/9947WDC-F	42
Trim	43
Wood door concealed	
placed by the 98/9950 WE e information./9949WDC-F	о С. 46
Trim	47
Wood door concealed vertical cable devices	

Von Duprin 98/99 Series • 3

51

Options and accessories

Applications & trim operation	Single & double door applications Door handing Outside trim operation Lever styles	Electrical options	RX Request to exit LX Latchbolt monitoring SS Signal switch CX Chexit [®] ALK Alarm kit E Electric mortise lock device
Trim options	ions Thumbpiece Lever		EL Electric latch retraction QEL Quiet electric latch retraction CON Allegion Connect
	Electrified outside lever trim (E996L) Breakaway lever Thumbturn control	Electrical accessories	Power supplies Electric power transfer
	Hospital pull Offset pull Vandal resistant pull AD-Series adaptable electronic trim	Mechanical options	XP98/99 rim exit device WS Surface vertical rod exit device Less bottom rod AX Accessible device
Strike options			Pullman latch Dummy push pad Braille, embossed, knurled and safety glow (Luminescent) touchpads
Dogging options	options Hex key dogging Less dogging		Pneumatic controlled exit devices Pneumatic power transfer
Symbols	Dogging keys Special center case dogging Double cylinder	Device accessories	Glass bead kit Vertical rod and latch guard Cover plate kits Cylinders Mullions
		Additional	Sex bolts ANSI Function, grade & type
		information	Ul fire labeling and opening size

Finishes Standa


Standard & special finishes

Nomenclature – how to order

None	Standard	EL	99	27	-L	-16	-F	LBR	3'	US3	RHR
SD	Special dogging R/VR - panic only	<u> </u>			Ť		<u> </u>				
SD CD CX E QEL EL LX RX RX2 SS AX PL PN WS XP WS 98 99 99 None	Special dogging R/VR - panic only Cylinder dogging - panic only Chexit Electric locking mortise/lever Quiet electric latch retraction Electric latch retraction Latch bolt monitoring Request to exit Double request to exit Signal switch Accessible device Pullman latch Pneumatic latch retraction Surface vertical rod exit device Heavy protection - rim Tornado & hurricane tested										
27 47	Surface mounted vertical rod device Concealed vertical rod device										
47 47WDC 48	Concealed vertical rod device Concealed vertical rod wood door device Concealed vertical rod device										
49 49WDC	Concealed vertical cable device Concealed vertical cable wood door device										
57 75	Three-point latch device Mortise lock device										
AD	AD Trim (to come from client)										
DT EO	Dummy trim Exit only										
HL K	Hospital pull trim Knob										
K-BE K-DT	Knob - blank escutcheon Knob, rigid - dummy trim										
K-NL L	Knob, rigid - night latch Lever (classroom)										
L-BE L-DT	Lever - blank escutcheon Lever, rigid - dummy trim										
L-NL NL	Lever, rigid - night latch Night latch										
NL-OP TL	Night latch cylinder assembly, optional pull Turn lever										
TL-BE TP	Turn lever - blank escutcheon Thumbpiece										
TP-BE	Thumbpiece - blank escutcheon										
XX	Lever style 06 standard Optional 01, 02, 03, 05, 07, 12 (Handed), 16 (Omega), 17, 18, Accent, Asti, Merano, St	Annes									
F	Fire exit device										
-2	Double cylinder (rim & mortise only)										
LBR LBL	Less bottom rod Less bottom latch	_									
SG ALK	Safety glow (luminescent) touchpad Alarm kit		- -]			
ALK-AR1 ALK-AR3 ALK-AR6 CON	Auto-reset 1 ¹ / ₂ minute alarm kit Auto-reset 3 minute alarm kit Auto-reset 4 ¹ / ₂ minute alarm kit Allegion Connect										
2' 3' 4'	2' Device (2' door size) 27, 47 or 49 only 3' Device (2' 4"– 3' door size) 4' Device (2' 10"– 4' door size)										
Finishes	US3, US4, US10, US26, US26D, US28, 313, 31 US32D – 98 ONLY -AM Antimicrobial (available US26D and US										
-LHR -RHR	Left hand reverse Right hand reverse								\ /-	e Duesia (98/99 Sei

Popular double door applications


Single door applications



Single rim device

lock device

Door handing




Outside


Double door applications



Mortise lock and surface mounted or concealed vertical cable/rod device combination-same direction



Two rim devices with mullionsame direction



Two vertical rods—double egress

Two surface mounted vertical rod

devices-same direction (do not use


with overlapping astragal)

Night latch

Key retracts latch bolt. Lever or knob

is rigid. Use NL suffix, e.g. 996LNL.

Two fire exit hardware vertical cables/rods with auxilary fire latch-LBR option



Two concealed vertical cables/rods

Dummy

Outside trim operation

Trim operation lever or knob



Key locks and unlocks lever or knob. e.g., 996L (Classroom)

996L Breakaway[™] lever



The 996L Breakaway trim has become the standard lever trim offering on the 98L/99L Series devices. The Breakaway design is especially effective in areas where vandalism to door hardware is a problem. The design intent is to discourage costly repairs from becoming necessary. The Breakaway feature is not available on the NL (night-latch) or DT (dummy trim) versions.

(Storeroom)

Blank escutcheon



Lever or knob always active. Use BE suffix, e.g., 996L-BE. (Passage)

Lever or knob rigid for pull operation. Use DT suffix, e.g., 996L-DT.


374T/376T Series thumbturn control



Standard operation, key locks and unlocks thumbturn. Optional operation, key unlocks thumbturn, re-locks when key is removed. This operation is created by changing the cylinder plate included with control. Use 11/4" mortise cylinder with a straight cam. Schlage cam reference L583-475. Use with a pull trim (990DT pictured).


Lever styles

Decorative levers



·· Available in Stainless Steel substrate ONLY.

Standard Levers



*Available in Stainless Steel - specify SS when ordering

9847-F/9947-F Concealed vertical rod fire exit device



9847-F/9947-F Fire exit concealed vertical rod device for use on pairs of doors up to 8' x 10' (2438mm x 3048mm), UL listed for fire exit hardware. See page 76 for detailed information on UL listed fire exit hardware label and door opening size information. Devices are ANSI A156.3 – 2008 Grade 1. The 9847-F device has a smooth mechanism case and the 9947-F device has a grooved case. The concealed vertical rod device is non-handed except when the following device option is used: SS (signal switch) devices. See opposite page for available outside trim and functions.

Finishes – US3, US3A, US4, US4A, US10, US26, US26D, US26D-AM Antimicrobial, US28, 313, 315 & 643E. US15 and US32D available with 98 Series only.



Specifications

Device functions	Device ships EO/DT/NL. Field selectable. For TP, K or L remove	PN	
Device lengths	NL drive screw from device. 2' 2' (610 mm) Door size 3' 2'4' to 3' (711mm to 914 mm) Door size 4' 2'10" to 4' (864 mm to 1219 mm) Door size	Pneumatic latch retraction • For areas where electrical devices banned	
Device centerline from finished floor	39⁵/₅" (1006 mm) Standard Adjustable from 35⁵/₅" (905mm) to 49⁵/₅" (1260mm)	Special linkage for mechanical or	
Center case dimensions	8" x 2³/₄" x2³/₅" (203mm x 70mm x 60mm)	pneumatic dogging	
Mechanism case dimensions	2¼" x 2¼" (57mm x 57mm)	EL Flastria latak	QEL Oviat alestria
Projection	Pushbar neutral – 3 ¹³ /16" (97 mm) Pushbar depressed – 3 ¹ /16" (78 mm)	Electric latch retraction • Enables remote	Quiet electric latch retraction • Bolt retraction via
Latch bolt	Deadlocking top & bottom bolt, 5/8" (16mm) throw	unlatching	switch
Door undercut	¹ / ₄ " (7mm) recommended	Alternative to manual dogging	Converts exit door to push-pull
Top & bottom Latch case	3 ³ / ₄ " x 1 ¹ / ₂ " x 1" (95mm x 38mm x 25mm)		operation
Vertical rods	Round 2-piece adjustable rods – Top rod adjustable from 6'8" (2027mm) to 8'4"(2533mm). Bottom rod adjustable 35 ⁵ / ₆ " (905 mm) to 49 ⁵ / ₈ " (1260 mm). Extension rod kits available for doors over 8'4" (2533mm). Includes screw pack for 1 ³ / ₄ " (44mm) to 2 ¹ / ₄ " (57mm) thick	E (E996L) Electrified breakaway lever • Electrified remote locking/unlocking	LX Latchbolt monitor switch • Signals use of an opening
Fasteners & sex bolts (SNB)	metal doors. Optional 425 SNB available.	Standard in fail safe condition	SPDT switch to monitor latch bolt
Electric options	LXLatchbolt monitor switchRXPushpad monitor switchRX2Double pushpad monitor switchEElectric unlocking and locking trimELElectric latch retractionQELQuiet electric latch retractionSSSignal switchCXChexit delayed exitALKAlarm exit kitWP-RXWaterproof request to exit	RX Pushpad monitor switch • Signals use of an opening • SPDT switch to monitor pushpad	CX Chexit delayed exit • Meets NFPA 101 requirements • Self-contained controls, locking, alarm
Mechanical options	CONAllegion ConnectLBRLess bottom rodPNPneumatic latch retractionGBKGlass bead kitSNBSex boltsSECSecurity screwsSLMSpecial laminate material blocking	ALK Alarm exit kit • Unauthorized opening triggers 85-decibel horn • Set in armed or disarmed mode	CON Allegion Connectors • Common connectors to connect various door hardware all
Dogging option	No mechanical dogging. EL and QEL option available	by key	the way to the power supply
Strikes	Top – 338 - Unfinished, Bottom – 385A - Unfinished		- 2110. 00ppt.)

	EO	DT	NL	NL-OP	TL 💼	TL-BE
	No outside trim Exit only	Dummy trim Pull when dogged (not recommended for fire device)	Night latch Key retracts latchbolt	Night latch Key retracts latchbolt optional pull required	Thumbturn Key locks & unlocks (use with DT trim)	Thumbturn Blank escutcheon always operable (no cylinder) (use with DT trim)
Product description	9847EO-F 9947EO-F	-	9847NL-F 9947NL-F	9847NL-OP-F 9947NL-OP-F	9847TL-F 9947TL-F	9847TL-BE-F 9947TL-BE-F
Trim description	-	990DT	990NL-R/V	110NL-MD	376T X 990DT	376T-BE X 990DT
Escutcheon plate size	_	3" x 14 ¹³ / ₁₆ " x ³ / ₃₂ " (76x360x2mm)	3" x 14 ¹³ / ₁₆ " x ³ / ₃₂ " (76x360x2mm)	_	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)
Pull center to center	-	5 ¹ / ₂ " (140mm)	5 ¹ / ₂ " (140mm)	_	-	_
Projection	-	2" (51mm)	2" (51mm)	_	2" (51mm)	2" (51mm)
ANSI function	01	02	03	03	11 or 12	16
Cylinder type	-	-	Rim	Rim	1 ¹ / ₄ " Mortise	_
Handing	-	-	—	_	-	—
Optional trim	x990EO x996EO	x996K-DT x996L-DT x696DT x697DT	x996K-NL x996L-NL x696NL x697NL			
#425 SNB optional - HMD req. WD w/o SLM pkg.	6	2	2	б	2	2

	L	L-NL	L-BE	L-DT
	Lever Key locks & unlocks	Lever – night latch Key retracts latchbolt	Lever – blank escutcheon Always operable (no cylinder)	Lever dummy trim pull when dogged
Product description	9847L-F 9947L-F	9847L-NL-F 9947L-NL-F	9847L-BE-F 9947L-BE-F	_ _
Trim description	996L-R/V*	996L-NL-R/V	996L-BE-R/V*	996L-DT
Escutcheon plate size	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)
Pull center to center	—	—	—	—
Projection	2 ⁷ /8" (73mm)	2 ⁷ /₃" (73mm)	2 ⁷ /₃" (73mm)	2 ⁷ /₃" (73mm)
ANSI function	08	03	14	02
Cylinder type	Rim	Rim	-	—
Handing	Handed/Reversible	Handed/Reversible	Handed/Reversible	Handed/Reversible
#425 SNB optional - HMD req. WD w/o SLM pkg.	2	2	2	2

* Electrified lever operation available

98/99 Finishes

Finishes*

Color	US number	BHMA number
Chromium, polished	US26	625
Anodized, aluminum	US28	628
Chromium, dull	US26D	626
Brass, polished	US3	605
Brass, dull	US4	606

	number	number
Bronze, dull	US10	612
Satin nickel Available for 98 ONLY	US15	619
Satin stainless steel	US32D	630
Duranodic dark bronze	313	710
Black, painted (not flat powder)	SPBLK	693
Flat Black	US19/ 315	622/711
Aged bronze	_	643e

US

внма

Color

Special finishes

Color	US number	BHMA number
Satin chrome, Antimicrobial	US26D- AM	626-AM
Satin stainless steel, antimicrobial	US32D- AM	630-AM

Pushpad options - Knurled

Embossed "Push"

Braille (Caution-Stairwell), satin stainless steel only

RSS - (Emergency Exit - Push to open and sound alarm) - Red Silkscreen lettering on US32D

* Note: Durable powder coated finishes available at specific special request. PLEASE CONTACT FACTORY.