

Popular double door applications


Single door applications




Double door applications



Mortise lock and surface mounted or concealed vertical cable/rod device combination-same direction




Two rim devices with mullionsame direction




Two vertical rods—double egress


Door handing




Outside



Two surface mounted vertical rod devices-same direction (do not use with overlapping astragal)



Two fire exit hardware vertical cables/rods with auxilary fire



Two concealed vertical cables/rods

Outside trim operation

Trim operation lever or knob

Standard

Key locks and unlocks lever or knob. e.g., 996L (Classroom)

Night latch



Key retracts latch bolt. Lever or knob is rigid. Use NL suffix, e.g. 996LNL.

Blank escutcheon



Lever or knob always active. Use BE suffix, e.g., 996L-BE. (Passage)

Dummy



Lever or knob rigid for pull operation. Use DT suffix, e.g.,

996L Breakaway™ lever



The 996L Breakaway trim has become the standard lever trim offering on the 98L/99L Series devices. The Breakaway design is especially effective in areas where vandalism to door hardware is a problem. The design intent is to discourage costly repairs from becoming necessary. The Breakaway feature is not available on the NL (night-latch) or DT (dummy trim) versions.

374T/376T Series thumbturn control



Standard operation, key locks and unlocks thumbturn. Optional operation, key unlocks thumbturn, re-locks when key is removed. This operation is created by changing the cylinder plate included with control. Use 11/4" mortise cylinder with a straight cam. Schlage cam reference L583-475. Use with a pull trim (990DT pictured).

Standard trim						
	No outside trim	Dummy trim Pull when dogged	NL Night latch Key retracts latchbolt	NL-OP Night latch Key retracts latchbolt optional pull required		
Product description	98EO 99EO	98DT 99DT	98NL 99NL	98NL-OP 99NL-OP		
Trim description	_	990DT	990NL-R/V	110NL-MD 110NL-WD		
Escutcheon plate size	_	3" x 14 ¹³ / ₁₆ " x ³ / ₃₂ " (76x360x2mm)	3" x 14 ¹³ / ₁₆ " x ³ / ₃₂ " (76x360x2mm)	_		
Pull center to center	_	5½" (140mm)	5½" (140mm)	_		
Projection	_	2" (51mm)	2" (51mm)	_		
ANSI function	01	02	03	03		
Cylinder type	_	_	Rim	Rim		
Handing	_	_	_	_		
Optional trim	x990EO x996EO	x996K-DT x996L-DT x696DT x697DT	x996K-NL x996L-NL x696NL x697NL			
Optional #425 SNB	6	2	2	6		

		L-NL C	L-BE	L-DT
	Lever Key locks & unlocks	Lever – night latch Key retracts latchbolt	Lever – blank escutcheon Always operable (no cylinder)	Lever dummy trim pull when dogged
Product description	98L 99L	98L-NL 99L-NL	98L-BE 99L-BE	98L-DT 99L-DT
Trim description	996L-R/V*	996L-NL-R/V	996L-BE-R/V*	996L-DT
Escutcheon plate size	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)	2 ³ / ₄ " x 10 ³ / ₄ " x ²⁷ / ₃₂ " (70x273x21mm)
Pull center to center	_	_	_	_
Projection	2 ⁷ / ₈ " (73mm)			
ANSI function	08	03	14	02
Cylinder type	Rim	Rim	_	_
Handing	Handed/Reversible	Handed/Reversible	Handed/Reversible	Handed/Reversible
Optional #425 SNB quantity for device	2	2	2	2

^{*} Electrified lever operation available

Notes