



# Popular double door applications


## Double door applications




Mortise lock and vertical rod device combination — same direction  
\*hollow metal only



Two rim devices with mullion — same direction



Two vertical rods — double egress



Two vertical rod devices — same direction (do not use with overlapping astragal)

## Door handing

Left hand reverse orientation



Right hand reverse orientation



**LHR**  
(Left hand reverse)



**RHR**  
(Right hand reverse)

Outside

# Outside trim operation

## Trim operation lever

### Standard operation




Key locks and unlocks lever.

### NL Function



Lever is locked when key is removed.  
(ANSI 09 function)

### Blank escutcheon



Lever always active. BE suffix,  
E.G., 371L-BE.

## Standard trim

### Series 550

Heavy aluminum bracket 10" (25mm) with stainless steel or brass pull bar. 550DT with NL function is furnished with 110MD or WD rim device. On 555NL (Metal) and 556NL (Wood), the cylinder locates in pull return. Cylinder must be ordered separately.



550DT



555NL  
(5547 only)



556NL  
(5547WDC only)

### Series 376T

Thumbturn control has a forged brass 7/8" (25 mm) thick escutcheon. Often used with DT trim or pull. An NL cylinder plate is included with thumbturn control for night latch operation if required. BE blank escutcheon is available, specify 376T-BE.



376T



375L (5575-F)




### Series 370L

Lever control has a forged brass 7/8" (25 mm) thick escutcheon. Optional lever designs are available. An NL cylinder plate is included with lever control for night latch. BE Blank escutcheon is available, specify 371L-BE.



371L (5547-F)  
376L (5547/5547WDC)  
379L (55 Rim)

Standard trim

	EO	DT	NL	L
				
	Exit only	Dummy trim Pull when dogged	Night latch Key retracts latch bolt	Lever Locks/unlocks
Product description	55EO	55DT	55NL	55L
Trim description	—	550DT	550DT/110MD	379L
Escutcheon plate size	—	—	—	7½" x 1⅞"
Pull overall length	—	3⅝" x 11 9/16"	3⅝" x 11 9/16"	—
Pull center to center	—	10"	10"	—
Projection	—	2 5/8" x 1 7/8"	2 5/8" x 1 7/8"	2 5/8"
ANSI function	01	02	03	08
Cylinder type	—	—	Rim	Mortise
Handing	Handed	Handed	Handed	Handed
Sex bolts furnished	4	4	4	—

Notes