

1741

Five Knuckle Plain Bearing Hinge

Application:

- ANSI A5134
- Reversible
- Square corners
- Removable pin



PRODUCT SPECIFICATIONS

MATERIAL:

- Steel with steel pin

FINISHES:

- 3 x 3: USP, 2D, US3, US10A, US26, US26D
- 3.5 x 3.5: USP, 1D, 2D, US3, 3LB, US4, ABA/US5, US10A, US10R, US15, AN/US15A, US26, US26D
- 4 x 4: USP, 1D, 2D, US4, ABA/US5, US10A, US10R, US15, AN/US15A, US26, US26D

NOTES:

- Hager residential hinges are provided without lubrication. We recommend lubricating the hinges after installation.
- All residential hinges conform to the "Light Weight" requirements of ANSI A156.1.

PRODUCT SIZE OPTIONS

HINGE SIZE (INCHES)	HINGE SIZE (MM)	HOLE COUNT	GAUGE OF METAL	PIN DIAMETER	SCREW SIZE (WOOD)
3 x 3	76 x 76	6	.085	.234	3/4 x 9 FH
3-1/2 x 3-1/2	89 x 89	6	.085	.234	3/4 x 9 FH
4 x 4	102 x 102	8	.085	.234	3/4 x 9 FH