

1756

185 Degree Door Viewer

Notes:

- Requires 9/16" (14 mm) hole for viewer
- For doors 1-3/8" (35 mm) to 2-1/8" (54 mm) thick, adjustable
- Tamper resistant
- 90 minute fire rated
- One way viewer



PRODUCT SPECIFICATIONS

MATERIAL:

- Brass

CERTIFICATIONS:

- Meets ANSI A156.16 for L03223

FINISHES :

- US3, US4, US5, US10A, US15, US15A, US26, US26D