

# **Card Printing Solutions**



Kantech's badging printers produce colorful, durable photo cards. Our printers are simple to use and virtually maintenance free. We have bundled our printers together with a High Definition portable Webcam, ribbon cartridge and cleaning supplies to form a complete badging kit and to keep your printer running like new. Our solutions easily adapt to evolving security and printing needs.

	DTC4250e Card Printer	DTC4500e Card Printer	HDP5000 Card Printer	
Overview and Key Features				
	The DTC4250e combines versatility with simplicity to easily print what you need. It is ideal for flexible, easy/reliable color printing and encoding. Its sleek design with changeable footprint can accommodate office environments where space is an issue. And a graphical display with easy-to-follow prompts ensures you'll always know printer status. Inline card printing and card encoding is accomplished using USB or optional Ethernet connectivity. The DTC4250e is ideal for medium-sized businesses, schools and governments seeking versatility in a convenient, professional and secure printer/encoder system.	The versatility of the DTC4500e is unsurpassed. Empowered by an extremely robust and highly-reliable print engine, this high-volume printer delivers speed, power and versatility rolled into one. High-capacity ribbons enable the DTC4500e to print twice as many full-color cards as most printers before the ribbon has to be changed. The DTC4500e combines high security and convenience to easily print what you need, including standard dual-input card hopper for increased capacity or management of multiple card types. And easy integration into existing IT infrastructures through the built-in Ethernet and USB connection, allowing for centralized or remote ID card issuance.	HDP5000 produces cards with superior print quality, higher reliability/durability and greater security. Taken together, these lower your total cost of ownership and make High Definition Printing available to practically any business. Uses a cartridge-based card handling system for faster reloading/card stock switching. By printing a reverse image on the underside of HDP Film, then fusing the film to the card surface, the HDP5000 creates an image quality that looks more like a sharp glossy photo than an ordinary ID badge. The cards are tamper-evident — if a counterfeiter tries to peel apart the layers, the image essentially destroys itself. USB and Ethernet connectivity is included, as is an internal print server for secure network printing.	
Specifications	Overview			
Print Method	Dye-Sublimation/Resin Thermal Transfer	Dye-Sublimation/Resin Thermal Transfer	HDP Dye-Sublimation/Resin Thermal Transfer	
Resolution	300 dpi (11.8 dots/mm) continuous tone	300 dpi (11.8 dots/mm) continuous tone	300 dpi (11.8 dots/mm) continuous tone	
Colors	Up to 16.7 million/256 shades per pixel	Up to 16.7 million/256 shades per pixel	Up to 16.7 million/256 shades per pixel	
Approximate Print Speed	24 seconds per card (YMCKO*)	24 seconds per card (YMCKO*)	37 seconds per card (YMCK* with transfer and dual-sided, simultaneous lamination)	
Accepted Standard Card Sizes	CR-80: 85.6 x 54 mm (3.370 x 2.125 in) and CR-79 Adhesive Back: 84.1 x 52.4 mm (3.313 x 2.063 in)	CR-80: 85.6 x 54 mm (3.370 x 2.125 in) and CR-79 Adhesive Back: 84.1 x 52.4 mm (3.313 x 2.063 in)	CR-80: 85.6 x 54 mm (3.370 x 2.125 in)	
Accepted Card Thickness	.229 - 1.016 mm (.009040 in)	Print Only: .229 - 1.016 mm (.009040 in); Print/Lamination: .762 - 1.02 mm (.0304 in)	Print only and Print/Lamination: .762 to 1.27 mm (.030050 in)	
Print Area	CR-80 edge-to-edge, CR-79: 83.8 x 51.8 mm (3.3 x 2.04 in)	CR-80 edge-to-edge CR-79: 83.8 x 51.8 mm (3.3 x 2.04 in)	CR-80 Over-the-edge	
Software Drivers	Windows XP / Windows Vista (32 bit & 64 bit) / Server 2003 & 2008 / Windows 7 / Windows <sup>®</sup> 8 (32 bit & 64 bit) / MAC OS X 10.5/10.6/10.7/10.8 / Linux	Windows XP / Windows Vista (32 bit & 64 bit) / Server 2003 & 2008 / Windows 7 / Windows <sup>®</sup> 8 (32 bit & 64 bit) / MAC OS X 10.5/10.6/10.7/10.8 / Linux	Windows 2000/XP/Server 2003/Vista (32 & 64 bit)/7 (32 & 64 bit); Mac OS X v10.4/v10.5/Linux	
Interface	USB 2.0, optional Ethernet with internal print server	USB 2.0 And Ethernet with internal print server	USB 2.0 And Ethernet with internal print server	
Input Capacity	100 cards (.762 mm/.030 in) Hopper	Dual-Input Card Hopper (200 cards)	100 cards (.762 mm/.030 in) Cartridge	
Output Hopper Card Capacity	Up to 100 cards (.762 mm/.030 in)	Up to 100 cards (.762 mm/.030 in)	200 cards (.762 mm/.030 in)	



#### **Plug and Play ID Photo Capture**



Logitech HD Portable Webcam C615 with Autofocus takes dazzling 8MP photos that will be suitable for any photo badging needs. Auto Light Correction adjusts for dim and harsh lighting so that photos

look natural and shadow-free It has a 360-degree full motion rotational camera, has fold-and-go portability and includes a tripod-ready base. Compatible with EntraPass security management software.

## **Badging Solutions Selection Chart**

Model Number	Description	
Badging Kits		
BK-1-A	FA-52000 printer, ID-DIGCAM Logitech HD Portable Webcam, FA-45100 YMCKO* ribbon cartridge and FA-44260 cleaning rollers	
BK-2-A	FA-52100 printer, ID-DIGCAM Logitech HD Portable Webcam, FA-45100 YMCKO* ribbon cartridge and FA-44260 cleaning rollers	
BK-2BC-A	FA-52100 printer, ID-DIGCAM Logitech HD Portable Webcam, FA-45110 YMCKOK* ribbon cartridge and FA-44260 cleaning rollers	
BK-2BCL-A	FA-55520 printer, ID-DIGCAM Logitech HD Portable Webcam, FA-45210 YMCKOK* ribbon cartridge, FA-47725 cleaning rollers and FA-82601 PolyGuard clear overlaminate.	
Printers		
FA-52000	DTC4250e single-sided printer, USB 2.0 and Ethernet with internal print server, 100 card input hopper. Ribbon cartridge sold separately.	
FA-52100	DTC4250e dual-sided printer, USB 2.0 and Ethernet with internal print server, 100 card input hopper. Ribbon cartridge sold separately.	
FA-55520	DTC4500e dual-sided printer, USB 2.0 and Ethernet with internal print server, 200 card dual-input hopper, lamination module; and bar code printer. Ribbon cartridge sold separately.	
FA-89003	HDP5000 dual-sided printer, USB 2.0 and Ethernet with internal print server, 100 card input cartridge. Ribbon cartridge sold separately.	
Ribbon Cartridg	yes	
FA-45100	For DTC4250e printer. YMCKO* print cartridge with cleaning roller, produces 250 imprints.	
FA-45110	For DTC4250e printer. YMCKOK* print cartridge with cleaning roller, produces 200 imprints.	
FA-45210	For DTC4250e printer. YMCKOK* print cartridge with cleaning roller, produces 500 imprints.	
FA-84052	For HDP5000 printer. YMCKK*, produces 500 imprints. Must use with FA-84053 clear or FA-84054 holographic retransfer film.	
FA-84057	For HDP5000 printer. YMCKI*, produces 500 imprints. Must use with FA-84053 clear or FA-84054 holographic retransfer film.	
Cleaning Suppli	es	
FA-44260	For DTC4250e printer. Contains 3 cleaning rollers.	
FA-47725	For DTC4500e printer. Contains 3 cleaning rollers.	
FA-86177	For DTC4250e and DTC4500e printers. Contains 2 print head cleaning pens, 10 cleaning cards and 10 cleaning pads.	
FA-89200	For HDP5000 printer. Contains 4 print head cleaning swabs, 10 cleaning cards, 10 cleaning pads and 3 alcohol cleaning cards.	
<b>Badging Acces</b>	sories: Encoders, Consumables, Cables and Cameras	
FA-47709	ISO Magnetic Stripe encoder for DTC4250e and DTC4500e printer.	
FA-82601	PolyGuard Overlaminate (1.0 Mil - Overlaminate Clear - 250 Count) for use with DTC4500e and HDP5000 printers.	
FA-84053	Clear HDP retransfer film required for printing cards with HDP5000 printer. Yields 1,500 imprints.	
FA-84054	High secure (prevents tampering and counterfeiting) orbit design holographic retransfer film required for printing (composite type only) cards with HDP5000 printer. Not for use with thermal transfer lamination. Yields 500 cards.	
FA-81754	CR-80 size UltraCard 30mil PVC cards – package of 500 cards.	
FA-85625	USB 2.0 high speed interface cable, 1.8 m (6 ft)	
ID-DIGCAM	Logitech HD Portable Webcam with motorized tracking.	

\* Indicates the ribbon type and the number of ribbon panels printed where Y=Yellow, M=Magenta, C=Cyan, K=Resin Black, I=Inhibit, O = Overlay

# **Related Products**









Approvals





ioProx Proximity Cards ioProx KT Proximity Readers 4-I

KT-400 4-Door Controller EntraPass Security Management Software

### www.kantech.com

© 2014 Tyco Security Products. All Rights Reserved. KT0250-DS-201409-R02-LT-EN

Product offerings and specifications are subject to change without notice. Actual products may vary from photos. Not all products include all features. Availability varies by region: contact your sales more sentative.