

Recreational Fire Extinguisher

Part number 21010207

Multipurpose use

Disposable

UL Rated 1-A, 10-B:C



Description

Suitable for use on Class A (trash, wood & paper), Class B (liquids & gases) and Class C fires (energized electrical equipment).

The Recreational unit is fitted with a pressure gauge that provides at-a-glance status, is manufactured from lightweight aluminum and a tough nylon valve assembly.



Includes bracket (896698R)

Features

- Easy-to-read gauge tells you fire extinguisher is charged and ready for use
- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Rust and impact resistant nylon handle
- 2.5 lb. of fire extinguishing agent (Average)
- 6 year limited warranty
- UL approved strap retention bracket
- Coast Guard (U.S.C.G) approved when fitted with supplied mounting bracket

At a Glance

- Model FA110
- Multipurpose Dry Chemical
- UL listed
- UL rated 1-A, 10-B:C
- U.S.C.G, DOT approved
- Supplied with retention strap bracket
- Monoammonium Phosphate
- 6 year limited warranty
- Suitable for use on most common fires

For use on the following types of fire:



Pt # 21010207
UPC: 0-47871-10207-5
I2F - 10047871102072

Product Specification

Net agent weight (Average)	2.5 lb.
Unit weight (Average)	3.9 lb.
Diameter	3.25 inches
Height	13.75 inches
Discharge time	8-12 seconds
Discharge range	6-8 feet
Operating pressure	100 psi
Cylinder	Seamless aluminum
Valve, handle, lever	Nylon
Strap Bracket	U.S.C.G approved

Packaging Options



Packaging dimensions (inches)

	Depth	Width	Height
Carton	5.375	3.375	15.06
Master Pack	16.5	16.5	11.5