

6.5" In-Ceiling Speaker



R-1650-C

Perfect for those who want excellent performance, reliability and durability at an affordable price, the R-1650-C brings dynamic acoustic performance to both home and commercial environments.

The R-1650-C employs a 6.5-inch polymer-cone woofer and a large motor structure for high sensitivity. A coaxially mounted 1-inch polymer-dome tweeter distributes smooth, clear highs over a wide area.

The speaker's mounting system makes installation a breeze, while its paintable aluminum grille provides added rust protection in moisture-prone areas such as bathrooms, kitchens and saunas.

While the R-1650-C will fit into our latest IK-650-C installation kit, it can also be used in conjunction with the ME-650-C fire-rated enclosure.

- Good sensitivity and power handling
- Paintable to match ceiling
- Packaged individually

SPECIFICATIONS

frequency response	57Hz-20kHz +/- 3dB
power handling	35 watts (140 watts peak)
sensitivity	91dB @ 2.83V/1 meter
nominal impedance	8 ohms compatible
drive components	Two-way system using one 1" (2.5cm) polymer dome, tweeter and one 6.5" (16.5cm) poly woofer
dimensions	9.5" (24.1cm)
cutout dimensions	8.3" (21cm)
mounting depth	4.2" (10.6cm)
installation kit	IK-650-C (sold separately)
weight	5.1 lbs (2.3 kg)
accessories	ME-650-C fire-rated enclosure (sold separately)
built from	2006

www.klipsch.com
1-800-KLIPSCH

All specifications are subject to change without notice. ©2007

