
ESSEX RACKMOUNT POWER, 9 OUTLET W/ METER

PWR-9-RPM |



FEATURES & BENEFITS

Essex Rackmount Power units provide affordable power distribution in a compact, rackmount form factor. Designed for use in Essex racks, these rackmount units feature surge protection and filtering.



- Value priced power specially designed for the Essex collection
- Line to neutral surge protection and filtering, which eliminates noise
- Models available with local meter to display current, voltage and power draw
- UL Listed
- 15 Amps
- Flat black finish
- Space-saving 1 rackspace design
- Integrated circuit breaker
- Front-facing convenience outlet, 9 outlets total

SPECIFICATIONS

GENERAL INFO

Cable Type: Corded
Finish: Flat Black
UL Standards Tested: 1449
Termination: 9' cord* w/NEMA 5-15P Plug
Surge Protected: Basic

ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Panel Width: 19
Depth (US): 4.3356
Height (US): 1.7362
Width (US): 19
Rack Units: 1

TECHNICAL INFORMATION

Amps: 15
Mounting: Horizontal
Volts: 120
Number Of Outlets: 9