



## SNE SERIES RACK, SNE27D-4242-P1

SNE27D-4242-P1 |

### FEATURES & BENEFITS

The SNE Series Digital is configured for digital (IP based) security systems consisting of high-density cabling, network equipment, and servers. Optional Tool-Free Lever Lock™ system accommodates small devices including encoders, power supplies, and Access Control Systems. • Fully configured Security Network Enclosure with passive ventilation for data centers o 70% open area vented front door o Pair of split flush mount locking side panels o 2 pair of adjustable cage-nut rackrail (including 6mm hardware) o Lever Lock™ compatible (accepts all Lever Lock™ vertical 21" accessories) o 27" width o 42" overall depth o 42 rackspace o 100 6mm cage-nuts/rack screws included SNE Series Digital with passive cooling (front to rear) • 70% open area split rear door • Solid top with brush cable pass-through



- Lever Lock™ compatible (accepts all 21" vertical accessories)
- Configured for passive front-to-back cooling
- Includes 70% open front door and 70% open area split rear door
- Includes solid top with brush cable pass-through
- Includes pair of split flush mount locking side panels
- UTL/ETL listed and seismic certified
- Includes 2 pair of adjustable cage-nut rackrail
- Includes 100 6mm cage nuts and rack screws

### SPECIFICATIONS

#### GENERAL INFO

Gangable: Yes  
 Finish: Black Powder Coat  
 UL Standards Tested: UL2416  
 Component Type: Passive

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
Greenguard: Yes  
ETL Listed: Yes  
UL Listing No: E313734  
UL Standard: Yes

## **DIMENSIONS**

Usable Depth: 38.48  
Usable Height: 73.5  
Panel Width: 19  
Capacity Weight (US): 12000  
Depth (US): 43.15  
Height (US): 79.52  
Width (US): 27.6  
Rack Units: 42

## **TECHNICAL INFORMATION**

Rackrail Type: Cage Nut  
Static Load Capacity: 12000  
UL Load Capacity: 3000  
Material: Steel  
Mounting: Horizontal  
Seismic Rating: Yes