SD Format Standard Digital Wireless

D-22A 1-Channel, 1-Button Handheld Transmitter

• ORDER # SNT00016



D-22B 2-Channel, 2-Button Handheld Transmitter

ORDER # SNT00296

D-22C 2-Channel, 2-Button Independent Code Transmitter

ORDER # SNT00298

Features:

- Two test/operate pushbuttons (D-22A has one test/operate pushbutton)
- Test/operate LED
- Removable wall mounting clip
- Standard digital format: 256 selectable codes for each pushbutton
- · Powered by one 9-volt battery (included)
- Current consumption: 12 mA transmitting
- RF frequency: 303.875 MHz
- 2.16" W x 3.75" H x 0.88" D

D-22D 2-Channel, 2-Button Lockout Transmitter

ORDER # SNT00299

D-4B 4-Channel, 4-Button Handheld Transmitter

ORDER # SNT00048B



Features:

- Two test/operate pushbuttons
- Lockout operation: either button sends channel one, both buttons send channel two
- Test/operate LED
- Removable wall mounting clip
- Standard digital format: 128 selectable codes
- Powered by one 9-volt battery (included)
- Current consumption: 12 mA transmitting
- RF frequency: 303.875 MHz
- 2.16" W x 3.75" H x 0.88" D



Features:

- Four test/operate pushbuttons
- Test/operate LED
- Removable wall mounting clip
- Standard digital format: 64 selectable codes
- Powered by one 9-volt battery (included)
- · Current consumption: 12 mA transmitting
- RF frequency: 303.875 MHz
- 2.16" W x 3.75" H x 1" D

ET-1B Emergency Transmitter • ORDER # SNT00054B



Features:

- · 2-Button lockout operation
- Water-resistantIncludes neck chain
- Standard digital format: 256 selectable codes
- Powered by one 12-volt battery (included)
- RF frequency: 303.875 MHz
- 1.72" W x 1.72" H x 0.75" D

ET-2-12 Miniature Transmitter

• ORDER # SNT00055A



Features:

- · Famous "Panic Button" design
- 30-Inch neck chain included
- Test/operate LED, red button
- Type GP-23 12-volt alkaline battery supplied
- Standard digital format: 256 selectable codes
- RF frequency: 303.875 MHz
- 1.42" W x 2.2" H x 0.66" D

ET-2-19 Miniature Transmitter

ORDER # SNT00055



Features:

- Famous "Panic Button" design
- 30-Inch neck chain included
- Test/operate LED, white button
- Type GP-23 12-volt alkaline battery supplied
- Standard digital format: 256 selectable codes
- RF frequency: 303.875 MHz
- 1.42" W x 2.2" H x 0.66" D