
Linear Security Solutions

DX Format Supervised Wireless 06

DXT-21 2-Button, 1-Channel

- Handheld Transmitter
- ORDER # SNT00376



DXT-23 3-Button, 4-Channel Handheld Transmitter • ORDER # SNT00377

DXT-25 5-Button. 8-Channel

Handheld Transmitter • ORDER # SNT00378

Features:

- Unique "Extra" top button
- · High visibility operate LED
- Two type 2032 lithium batteries supplied
- Pocket/belt clip supplied
- DX format
- RF frequency: 315 MHz
- 1.6" W x 4.2" H x 0.8" D

NOTE:

DX format transmitters are supervised for low-battery reporting only. Hourly status reports are not sent from DX format transmitters.

DXT-601 1-Button,

- 1-Channel Key Ring Transmitter
- ORDER # SNT00410



Features:

- Two type 2016 lithium batteries supplied
- Detachable key ring supplied
- DX format
- RF frequency: 315 MHz
- 1.25" W x 2.25" H x 0.48" D



Features:

- Alarm and low-battery transmissions
- Walk-test mode
- Fresnel lens with 24 facets
- Battery saver circuitry
- 9-Volt alkaline battery supplied
- DX format
- RF frequency: 315 MHz
- 3.2" W x 4.4" H x 1.75" D

DXT-61A 1-Button, 1-Channel Pendant Transmitter

ORDER # SNT00380A



Features:

- Famous "Panic Button" design
- 30-Inch neck chain included
- Test/operate LED
- Type GP-23 12-volt alkaline battery supplied • DX format
- RF frequency: 315 MHz
- 1.42" W x 2.2" H x 0.66" D

DXT-81 Bill Trap Transmitter

• ORDER # SNT00383



DXT-41 1-Channel, 1-Button Key Ring Transmitter

ORDER # SNT00381



DXT-31

- Door/Window Sensor
- ORDER # SBT00014



Features:

- · Alarm, alarm restore, and low-battery transmissions
- Includes mounting shoe
- External contact terminals
- N/O or N/C input loop circuit
- (included)

Features:

- Low-battery reporting only when cash drawer is open
- Alarm, restore, test transmissions
- Lithium battery-powered
- Test LED
- · Transmit repeat feature ensures reliability
- DX format
- RF frequency: 315 MHz
- 2.4" W x 4.5" H x 0.8" D

DXT-42 3-Channel, 2-Button Key Ring Transmitter

ORDER # SNT00382

Features:

- Two type 1620 lithium batteries supplied
- Detachable key ring supplied
- DX format
- RF frequency: 315 MHz
- 1.25" W x 2.25" H x 0.48" D



- Includes magnet for internal contact
- DX format
- Powered by two 2032 lithium batteries

• RF frequency: 315 MHz

• 1.6" W x 3.4" H x 1.2" D