


FULL HD 1080p

LED

PREMIUM WIDE



27REDP

BUILT TO RUN 24 X 7 X 365 CONTINUOUSLY

OVERVIEW

The ORION PREMIUM WIDE Series is our high performance, feature rich monitor line with an All Metal Cabinet, PIP / PBP, Dual Analog In, Auto Source Sequencing (up to 7 sources), Trigger Alarm / Sensor, 3D Comb Filter, Deinterlace, Noise Reduction. This series has the versatility and configuration options you need to support your security surveillance applications.

FEATURES

- » Metal Chassis
- » 1920 x 1080p FULL HD
- » PIP / PBP Multi Display Function
- » 3D Comb Filter / Deinterlace, Noise Reduction, Advanced Auto Power Recovery, Auto Source Sequencing, Trigger Source Switching, Auto Pixel Shift Multi-Language Support
- » BNC Video 2 In / 2 Out, S-Video 1 In / 1 Out, VGA 1 In, DVI-D 1 In, HDMI 2 In, Audio 2 In, PC Stereo 1 In
- » Built-In Speakers
- » Wall and Rack Mount Kit




SPECIFICATIONS


27REDP	
Display	
Screen Size	27 Inch
Max. Resolution	1920 x 1080 @ 60Hz
Pixel Pitch	0.3114 x 0.3114mm
Brightness	250cd/m ²
Contrast Ratio	1000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	178° / 178°
Display Color	16.7 Million
Response Time	< 8ms (Gray to Gray)
Video System	NTSC / PAL
Interface	
Video In / Out (BNC Type)	2 In / 2 Out
S-Video In / Out	1 In / 1 Out
DVI-D In / HDMI In	1 In / 2 In
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	2 Left & Right
PC Stereo In	1 In
Transmitter	
Remote Control	Yes
Audio	
Built-in Speakers	Yes (1W x 2)
Features	
Multi Display Function	PIP / PBP
Filter Type	3D Comb Filter
Deinterlacing	Yes
Advanced Auto Power Recovery	Yes
Noise Reduction Control (NR)	Yes
LCD Protection Glass	N/A
Auto Pixel Shift	Yes
Auto Source Sequencing	Yes
Trigger Sensor	Yes (NO / NC)
Multi Language	English, Spanish, French, German, Italian
General	
Outline Dimension (w/ stand)	24.92" x 16.59" x 5.91"
Net Weight	8.5Kg (18.74 lbs)
Material / Color	Electronic galvanized iron / Black
Desk Top Stand	Yes
Part / Labor	3year / 3year
Consumption: < On	< 40W
	AC100 ~ 240V(50/60Hz)
Operating Temperature	0° ~ 40° C / 32° ~ 104° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
Mounts	
VESA™ Mount Size	200 x 100mm
Wall	WB-31, WB-2642
Ceiling	CMK-01

*Design and specifications are subject to change without notice


INPUT INTERFACE



DIMENSIONS



OPTIONAL MOUNTS



ADVANTAGES

3D Comb Filter, Noise Reduction and Deinterlacing provides high quality color producing the best color sense

Dual Screen Display / Dual Signal In (Analog & Digital)

Picture-in-Picture (PIP) mode allows an image from an AV source to be displayed as a picture within the image from a PC source (or vice-versa). Picture-by-Picture (PBP) mode permits images from an AV and PC source to be displayed side by side for split-screen viewing.



Auto Pixel Shift

Minutely moves pixels diagonally to prevent after-image / static image burn in

