

UNIVERSAL 26-BIT WIEGAND READER









- 26-Bit Wiegand Proximity Reader
- Range up to 2 inched
- Solid Epoxy Potted
- External LED
- External Buzzer
- Indoor or outdoor

24 months warranty

TECHNICAL SPECIFICATION

POWER INPUT: 5.0 - 12 VDC CURRENT CONSUMPTION: 50-100 mA

Output Format: 26bit Wiegand

OPERATING ENVIRONMENT: -31°F to +149°F

Reading Time (Card): 30ms.

External LED Control, External Buzzer Control

LED Indicator: 2 Color LED Indicators(Red and Green)

Beeper Piezo Buzzer Color: Charcoal

Material: Polycarbonate Shipping Weight: 1 lbs

ORDERING PART NUMBER

UWCR

UWCR OPTIONS AND ACCESSORIES

UISO ISO 26 bit wiegand card (credit Card Size)
UFOB 26 bit wiegand keyfob
UCLAM 26 bit wiegand card with punch hole for badge holder
UCRM Universal 26-Bit Wiegand - RS485 Module

Specifications subject to change without prior notice

PACH AND COMPANY
Home of Telephone Access Control Systems



Phone: 1-888-678-7224 949-498-2951

www.pach-co.com