

VIDEO SECURITY LOCK BOX CABINETS

PRODUCT SPECIFICATION SHEET

345DLB ■ 245DLB ■ 245VSC ■ 185VSC ■ 134VSC ■ 245WMK



MFG. PART NO. 345DLB

DESCRIPTION: Digital/Video Media Security Cabinet
DIMENSIONS: 21" (W) x 24" (D) x 13" (H); WT: 50 LBS.

MFG. PART NO. 245DLB

DESCRIPTION: Digital/Video Media Security Cabinet
DIMENSIONS: 21" (W) x 24" (D) x 8" (H); WT: 42 LBS.

MFG. PART NO. 245VSC

DESCRIPTION: Digital/Video Media Security Cabinet
DIMENSIONS: 21" (W) x 21" (D) x 8" (H); WT: 39 LBS.

MFG. PART NO. 185VSC

DESCRIPTION: Digital/Video Media Security Cabinet
DIMENSIONS: 18" (W) x 18" (D) x 5" (H); WT: 25 LBS.

MFG. PART NO. 134VSC

DESCRIPTION: Digital/Video Media Security Cabinet
DIMENSIONS: 13" (W) x 14" (D) x 5" (H); WT: 12 LBS.

MFG. PART NO. 245WMK

DESCRIPTION: Wall Mount Bracket(s) Kit
DIMENSIONS: 24" Support Arm x 24" Wall Arm
WT: 10 LBS.

VIDEO SECURITY CABINETS

FEATURES

- Protection for DVR/VCR or video surveillance equipment.
- Removable lid and drop down front panel for access ease.
- Power Cord; AC High Efficiency Fan; Washable Fan Filter; Fan Finger Guard; and lock/keys included.
- Two cable pass through openings; and two optional knock out openings for ease in multi-cable applications.
- Pre-drilled holes for optional wall mount bracket.
- Heavy duty 16 gauge construction with durable powder coated finish.

SPECIFICATIONS

MATERIAL	Housing:	16 Gauge Cold Rolled Steel
	Fan:	UL Approved 120 x 38 mm. 120 V. AC High Speed, Ball Bearing, Terminal Ending
	Power Cord:	UL Approved 120V.
	Lock:	Stainless Steel Keyed Barrel
TYPE		Shelf and/or Wall Mount
FINISH		Durable Polyester-base UV Powder Coated Exterior



PACH AND COMPANY
HOME OF TELEPHONE ACCESS CONTROL SYSTEMS

AEGISANTUM

For Availability, call 1.888.678.7224 or 949.498.2951
For Product Spec. Sheets, visit www.pach-co.com