



F2164/2364 All-In-One Strikes

Versatile design features adjustable deadbolt keeper and deadlatch ramp allowing it to work with most locks. Faceplate: 1-1/4"W x 4-7/8"H (32mm x 124mm)

Insert Depth: 1-3/4"D (45mm)



375mA¹ Field-Selectable 12/24VDC, 12-24VAC2 Fire-Rated Optional 3-Hour



1,500lbf Static 70ft-lb Dynamic

Latch Monitor

Plug-In Latch Monitor

Accessory Available



Endurance 500,000 Cycles

5 Year Limited Warranty



Fail-Secure & Fail-Safe



Model Available³

212-24VAC not available with 2364 model

³Fire-rated (F) model only, 3-hour for single swing, 90-minutes for standard pair of doors



Saw-Tooth Adjustment Locator[‡]



Deadbolt Plug

- Versatile strike designed to work with most locks
- Accommodates 1/2" (12.7mm) to 3/4" (19mm) latch projection
- Adjustable deadbolt keeper and deadlatch ramp
- Accommodates up to 1" deadbolt (night-latch function only, bolt will not release)
- Plug-in wire connectors
- Runs cool solenoid design prevents keeper from heating up
- Trim plate included to cover up irregular frame cut-out
- Stainless steel ensures superior strength and creates a sleek aesthetic
- Includes two keeper shims 1/16" (1.5mm) and 1/8" (3mm) –for horizontal adjustment for misaligned frames (unique sliding design)
 - Non-handed
 - Factory tested to over 2-million cycles of operation
 - Brushed Stainless Steel (32D) finish
 - UL 294 Listed for Access Control Unit Accessory (6th Edition)
 - UL 1034 burglary-resistant Listed
 - UL 10C, 3-hour fire-rating Listed³
 - CAN/ULC S104, 3-hour fire-rating Listed³
 - California State Fire Marshal Listed (CSFM: 3776-2127:0103)3
- Certified to ANSI/BHMA standard A156.31, Grade 1, endurance 500,000 cycles
- Patent #: US 9,580,935









Options

• F – 3-hour fire-rating Listed

How To Order

Options					
F	— Fire-Rated⁴				
	2		64	Χ	32D
		1	-Fail-S	Secure	
		3	-Fail-S	Safe	
			Mode		

Example: F2164 x 32D

⁴Available in fail-secure mode only.

Accessories

Model	Description
F2LM	Latch monitor plug-in kit (2A @ 24VDC)
2FP	Filler plate (for use when replacing discontinued 2 Series models)
F2-19	Centerline faceplate, 1-3/8"W x 9"H (35mm x 229mm), 32D finish
F2-29	Offset faceplate, 1-3/8"W x 9"H (35mm x 229mm), 32D finish