

2-Channel RF Transmitters and Receiver

SK-919TD2A-UP*2-Button Pre-Coded Transmitter***SK-917T2A-UQ***2-Button CODEBUMP™ Transmitter*

- Range: Up to 500ft (152m)*, 315MHz
- LED Transmission indicator
- Includes 12VDC alkaline battery
- Compatible with all 315MHz SECO-LARM receivers
- SK-919TD2A-UP: 68 billion possible codes
- SK-917T2A-UQ: 18 quintillion possible codes



SK-919TD2A-UP



SK-919TP2H-NUQ

SK-919TP2H-NUQ*2-Button Handheld Transmitter*

- Range: Up to 500ft (152m)*, 315MHz
- Over 68 billion possible codes
- Includes two 3VDC lithium batteries
- Compatible with all 315MHz SECO-LARM receivers
- Visor clip and belt clip included. Belt-clip holster and wall-mount bracket also available (model #: SK-9HBC)
- Low battery indicator – LED flashes when battery drops below 2VDC



SK-910RB2Q

SK-910RB2Q*2-Channel Receiver*

- Five programmable relay output modes:
 - 4-Second momentary
 - 1-Second momentary
 - Toggle (ON/OFF)
 - Latch
 - Validity
- 11~24 VAC/VDC Operation
- Range: Up to 500ft (152m)*, 315MHz
- Independently programmable outputs
- Controls garage doors, gates, house lights, alarm panels or other devices via remote
- Two LEDs indicate RF reception, learn mode entered, transmitter learned, memory cleared, and relay output mode
- Pushbutton programming, no need to cut jumpers
- Up to 15 transmitter button codes per channel can be learned
- Compatible with all 315MHz SECO-LARM transmitters

*Actual range will vary greatly depending on the installation and operating environment

Also Available from SECO-LARM®:**SK-91ERSD**

Increase range up to 1,000ft (304m)* with the Extended Range Antenna

**SK-910RB2Q Specifications:**

Operating frequency		315MHz
Memory capacity		15 Transmitter button codes per channel, 30 total
Operating voltage		11~24 VAC/VDC
Operating current	Standby	8mA@12VDC
	Active	30mA@12VDC
Relay output modes		4-Sec momentary, 1-sec momentary, toggle, latch, validity
Relay contact rating		Form C 10A@24VDC/120VAC
Connectors		Screw terminals: Power (+,-) 1 relay per channel (NO/NC/COM)
Dimensions		3 7/16" x 3 7/16" x 1 1/8" (87x87x28 mm)

SECO-LARM® U.S.A., Inc.

16842 Millikan Ave, Irvine, CA 92606

Tel: 949-261-2999 / 800-662-0800 • Fax: 949-261-7326

sales@seco-larm.com • www.seco-larm.com



Copyright 2015 © SECO-LARM U.S.A., Inc. All rights reserved.
The SECO-LARM policy is one of continual development. For that reason, SECO-LARM reserves the right to change prices and specifications without notice. SECO-LARM is not responsible for misprints.

SECO-LARM® ENFORCER® CRIMEBUSTER® CBA SLI®

PISK-910RB2Q.docx