

# Switches and Buttons

## Tamper Switches

**SS-072Q** For normally closed tamper circuits

**SS-073Q** For normally open tamper circuits

- For drawers and alarm boxes
- Silver-plated contacts
- High-impact plastic case
- Screw terminals
- Rated 0.5A@50VDC



## Toggle Switches

**SS-076Q/GY** Gray toggle switch

**SS-076Q/SW** Snow-white toggle switch

- SPST Toggle switch rated 3A@125VDC
- Attractive plastic case with two screw holes
- Pre-wired 6" (15cm) leads



## Momentary Pushbuttons

**SS-032Q/RD** Red N.O. Button

**SS-033Q/BK** Black N.C. Button

- Fits 1/2" (13mm) hole
- Rated 1A@12VDC



SS-032Q/RD

SS-033Q/BK

## Momentary Pushbuttons

**SS-074/BG** N.O. Push-to-close operation

- N.O. (Push-to-close) Operation
- Double-button operation virtually eliminates accidental triggering
- Sturdy metal case, silver-plate SPST contacts, pre-wired for quick installation
- Rated 1A@25VDC



## Holdup Buttons

**SS-077Q** N.C. Push-to-open operation

**SS-078Q** N.O. Push-to-close operation

**SS-078-KEYQ** Spare key for SS-077Q and SS-078Q

- Latching pushbutton, flag shows when pressed
- High-impact ABS case, stainless steel cover
- SPST Switch rated 1A@12VDC
- Two reset keys included



## Vibration/Shock Sensors

**SS-040Q/BR** N.C., Brown

**SS-040Q/W** N.C., White

- Detects shock to window glass, walls, or ceilings
- Gold-plated contacts for longer life and reliability
- Built-in tamper switch for complete security
- Adjustable from 1~50g
- 1A@50VDC
- Size: 5/8"x7/8"x2 3/8" (16x22x60 mm)



## Foil connection block

**SS-202Q**



## Emergency Pushbuttons

**SS-075Q** N.O. "Emergency" button

**SS-075CQ** NO/NC "Emergency" button

**SS-075C-PEQ** NO/NC Emergency button kit

- SPST Contact rated 0.5A@12VDC
- Screw terminals for easy installation
- Large button with printed message on faceplate

### SS-075C-PEQ Only

- Includes three stick-on labels ("PUSH TO EXIT", "PRESIONE PARA SALIR", "EMERGENCY")
- SPST Switch rated 1A@12VDC

