ENFORCER® Wireless

4-Channel RF Transmitters and Receiver

SK-919TP4J-NUQ *4-Button Pre-Coded Transmitter*

SK-917TP4J-NU *4-Button CODEBUMP™ Transmitter*

SK-919TP4J-NUQ

- Range: Up to 500ft (152m)*, 315MHz
- LED Transmission indicator
- Attractive slimline design
- Over 68 billion possible codes
- Includes 12VDC alkaline battery
- Compatible with all 315MHz SECO-LARM receivers
- SK-917TP4J-NU: Code changes every time transmitter button is pressed

SK-919TP4H-NUQ *4-Button Handheld Transmitter*

SK-919TP4H-NUQ

- Range: Up to 500ft (152m)*, 315MHz
- Attractive slimline design
- Over 68 billion possible codes
- Includes two 3VDC lithium batteries
- Compatible with all 315MHz SECO-LARM receivers
- Visor clip and belt clip included. Belt-clip holster and wall-mount bracket also available (model #: SK-9HBC)
- Low battery indicator – LED flashes when battery drops below 2VDC

SK-910R4Q *4-Channel Receiver*

SK-910R4Q

- Five programmable relay output modes:
  - Timed
  - Momentary (1, 2, 3, 4, 5, 10, 30, or 60 sec)
  - Toggle (ON/OFF)
  - Latch
  - Validity
- 11~24 VAC/VDC Operation
- Range: Up to 500ft (152m)*, 315MHz
- Independently programmable outputs
- Controls garage doors, gates, house lights, alarm panels or other devices via remote
- Four LEDs indicate RF reception, learn mode entered, transmitter learned, memory cleared, and relay output mode
- Pushbutton programming, no need to cut jumpers
- Up to 15 transmitter button codes per channel can be learned
- Compatible with all 315MHz SECO-LARM transmitters

*Actual range will vary greatly depending on the installation and operating environment

Also Available from SECO-LARM®:

SK-91ERSD	
Increase range up to 1,000ft (304m)* with the Extended Range Antenna	

SK-910R4Q Specifications:

Operating frequency		315MHz
Memory capacity		15 Transmitter button codes per channel, 60 total
Operating voltage		11~24 VAC/VDC
Operating current	Standby	8mA@12VDC
	Active	30mA@12VDC
Relay contact rating		Form C 10A@24VDC/120VAC
Connectors		Screw terminals: Power (+,-), 1 relay per channel (NO/NC/COM)
Dimensions		$5^{5}/_{16}$"x$3^{15}/_{16}$"x$1^{1}/_{8}$" (135x100x28 mm)

SECO-LARM® U.S.A., Inc.
16842 Millikan Ave, Irvine, CA 92606
Tel: 949-261-2999 / 800-662-0800 • Fax: 949-261-7326
sales@seco-larm.com • www.seco-larm.com

Copyright 2013 © SECO-LARM U S A, Inc All rights reserved
The SECO-LARM policy is one of continual development For that reason, SECO-LARM reserves the right to change prices and specifications without notice SECO-LARM is not responsible for misprints
SECO-LARM® ENFORCER® CRIMEBUSTER® CBA SLI