



This basic LED annunciator is compatible with our full line of Infinity modules to build a custom annunciation solution that fits your every requirement.

SPECIFICATIONS

Tabular style annunciator with a white background and black grid comprised of four zones, each with red LED point illumination. LEDs are socketed for the times a yellow, green or other colored light is required. No modifications necessary to use the various commons and voltages with the exception of installing a plugable jumper for the 2 Volt option. 100% backwards compatible with the original IAM4Z. Up to 6 units can be mounted in the appropriately sized IGB box with accompanying IGP plate. Standard clinch type terminal strip used for field wiring.

FEATURES

- Common Positive or Negative
- Legend sheet protected by scratch-resistant Lexan® viewing window
- Durable steel frame mounts into an Infinity Gang Box or standard electrical back box and securely holds the Infinity Gang Plate
- Standard legend slip sheet and all mounting hardware included



RANGE RATING

27.2mA @18V | 50.5mA @32V

AGENCY APPROVALS

- UOXX.S2580 UL Listed Control Unit Accessories
- 7120-0553:0105 California State Fire Marshal (CSFM)

ORDERING INFORMATION

Part #	Description
IAM4Z (SSU02510)	4 Zone Annunciator Module