



SSM/SSV Series Alarm Bells

System Sensor's SSM and SSV series alarm bells are low current, high decibel notification appliances for use in fire and burglary systems or other signaling applications.



Features

- Approved for indoor and outdoor use
- Low current draw
- High dB output
- Available in six-inch, eight-inch, and ten-inch sizes
- AC and DC models
- DC models polarized for use with supervision circuitry
- Mount directly to standard four-inch square electrical box indoors
- SSM and SSV series come pre-wired

Reliable Performance. The SSM and SSV series provide loud resonant tones. The SSM series operates on 24VDC and are motor driven, while the SSV series operates on 120VAC utilizing a vibrating mechanism.

Simplified Installation. For indoor use, the SSM and SSV series mount to a standard four-inch square electrical box. For outdoor applications, weatherproof back box, model number WBB, is used.

The SSM and SSV series come pre-wired, to reduce installation time. The SSM series incorporates a polarized electrical design for use with supervision circuitry.

Agency Listings



SSM/SSV Specifications

Architectural/Engineering Specifications

Model shall be a SSM or SSV Series alarm bell. Bells shall have underdome strikers and operating mechanisms. Gongs on said bells shall be no smaller than nominal 6" / 8" / 10" (specify size) with an operating voltage of 24VDC or 120VAC (specify by part number). Bells shall be suitable for surface or semi-flush mounting. Outdoor surface mounted installations shall be weatherproof (using optional WBB weatherproof electrical box). Otherwise bells shall mount to a standard 4" square electrical box having a maximum projection of 2 1/2". Bells shall be located as shown on the drawings or as determined by the Authority Having Jurisdiction. Bells shall be listed for indoor/outdoor use by Underwriters Laboratories and the California State Fire Marshal, and approved by Factory Mutual and MEA.

Physical/Operating Specifications

Operating Temperature Range	-31°F to 140°F
Operating Voltage	SSM series: 24VDC SSV series: 120VAC
Termination	Provided with 2 sets of leads for in/out wiring
Service Use	Fire Alarm, General Signaling, Burglar Alarm
Warranty	3 years

Electrical Specifications

Model	Gong Diameter (inches)	Nominal Voltage	Operating Voltage Limit	Maximum Current	Sound Output (dBA)
SSM24-6	6	Regulated 24VDC	16 to 33VDC	DC-31.1mA/ FWR-53.5mA	82
SSM24-8	8	Regulated 24VDC	16 to 33VDC	DC-31.1mA/ FWR-53.5mA	80
SSM24-10	10	Regulated 24VDC	16 to 33VDC	DC-31.1mA/ FWR-53.5mA	81
SSV120-6	6	Regulated 120VAC	96 to 132VAC	53mA	85
SSV120-8	8	Regulated 120VAC	96 to 132VAC	53mA	82
SSV120-10	10	Regulated 120VAC	96 to 132VAC	53mA	82

* Sound output measured at Underwriter Laboratories, as specified in UL464

Ordering Information

UL/FM Model No.	ULC/Canadian Model No.	Description
SSM24-6	SSM24-6A	Bell, 6", 24VDC, Polarized, 82dBA
SSM24-8	SSM24-8A	Bell, 8", 24VDC, Polarized, 80dBA
SSM24-10	SSM24-10A	Bell, 10", 24VDC, Polarized, 81dBA
SSV120-6	SSV120-6A	Bell, 6", 120VAC, 85dBA
SSV120-8	SSV120-8A	Bell, 8", 120VAC, 82dBA
SSV120-10	SSV120-10A	Bell, 10", 120VAC, 82dBA
WBB		Weatherproof back box for SSM and SSV series, when installed outdoors



3825 Ohio Avenue • St. Charles, IL 60174
Phone: 800-SENSOR2 • Fax: 630-377-6495

©2011 System Sensor.
Product specifications subject to change without notice. Visit systemsensor.com for current product information, including the latest version of this data sheet.
A05-0260-010 • 08/11 • #2870