



STROBE

***SPECIAL ORDER ITEMS**



TANE SAFETY FLASH 2.0

***SPECIAL ORDER ITEMS**

Ordering Information

Part Number	Part Image	Part Size Inch(mm)	Rated Voltage	Operating Temp. Range	Strobe Light Current Draw	Flash Frequency	LUX (Lumens)	Order Qty	Order With (required Part)
* STROBE FM (XENON BULB) (Flange Mount)		2.9"(73.6) Dia 1.44"(36.5) H	12VDC	-20 ~ +60°C w/o loss of function	650mA/12VDC	105 +/- 20 per minute	15,000 LUX	1	Connect to panel box or other signal & power source. Available colors: Red, Blue, Clear, Yellow
* STROBE STD (XENON BULB) (Stud Mount)		3.03"(77) Dia 1.89"(48) H	12VDC	-20 ~ +60°C w/o loss of function	650mA/12VDC	105 +/- 20 per minute	15,000 LUX	1	Connect to panel box or connect in concert with our stainless steel BOX WSPR66A Exterior Siren Available colors: Red, Blue, Clear, Yellow
* STROBE FM LED (Flange Mount)		2.9"(73.6) Dia 1.44"(36.5) H	12VDC	-20 ~ +60°C w/o loss of function	650mA/12VDC	110 +/- 15 per minute	11,000 LUX	1	Connect to panel box or other signal & power source. Available colors: Red, Blue, Clear, Yellow
* STROBE STD LED (Stud Mount)		3.03"(77) Dia 1.89"(48) H	12VDC	-20 ~ +60°C w/o loss of function	650mA/12VDC	110 +/- 15 per minute	11,000 LUX	1	Connect to panel box or connect in concert with our stainless steel BOX WSPR66A Exterior Siren Available colors: Red, Blue, Clear, Yellow
* SAFETY FLASH 2.0		4.0"(101) Dia 4.5"(114) H	3VDC	NA	NA	60 +/- 5 per minute	88 LUMENS	1	Stand Alone Installation Magnetic Base Standard Available colors: Red, Blue, Yellow

***SPECIAL ORDER ITEMS - Call for Min. Order Qty. - Lead time - Pricing**



The Best Guarantee Since 1984 : \$50-1

TANE ALARM PRODUCTS

906 JERICHO TURNPIKE, NEW HYDE PARK, NY 11040

Tel: 800-852-5050 • 516-328-3351 • Fax: 516-326-9125

www.tanealarm.com • E-MAIL: info@tanealarm.com