

Features

- Call-placed indicator
- Call cancellation only at point of origin
- Attractive, flame retardant (UL[®] 94V-0) plastic faceplate
- Contacts to signal dome light, and buzzer or bell

Description

The SF118C Emergency Switch is available in two models. The SF118/2C provides two contacts, one to signal a dome light and master station, and one to signal a buzzer or DC bell. The SF118/4C provides two additional contacts that may be used to operate additional signaling devices as needed.

Both models feature a rugged, long-life, positive-acting switch mounted on an attractive, flame retardant (UL[®] 94V-0) plastic faceplate marked **EMERGENCY** that includes a red LED. Signaling an emergency requires just a short pull in any direction on the 6' long nylon cord. The signal cannot be canceled except at the point of origin.



SF118/2C, SF118/4C Emergency Call Station

Specifications

Dimensions:	Height: 4.5" (114 mm)
	Width: 2.75" (70 mm)
	Depth: 1.5" (38 mm)
Switch:	SF118/2C: 2 PDT
	SF118/4C: 4 PDT
Construction:	Switch and lamp are mounted to an attractive, flame retardant (UL [®] 94V-0) plastic faceplate.
Call-Placed Light:	Red LED.
Connections:	Wire leads.
Mounting:	Standard single-gang electrical box.

Required Components

CM800 Emergency Call System