



2-Port USB KVM Switch Kit

TK-207K (v1.3R)

- 2-port KVM switch with VGA and USB connections to computers
- Device monitoring with Auto-Scan and audible feedback
- High quality 2048 x 1536 resolution for a crisp display
- Support most operating systems and advance mouse designs
- All required cabling included

The 2-Port USB KVM Switch Kit lets you manage two PC's with just one set of keyboard, monitor, and mouse. Switch between two PC's with a simple press of a button! Separate sets of KVM cables are included with the KVM Switch, so users can start controlling 2 PC's instantly. The KVM cables also provide power to the KVM Switch, eliminating the need for a power adapter. Hot Key operations provide immediate access to features such as computer switching, and auto-scanning. With its Hot-Plug, and Audible Feedback, the 2-Port USB KVM Switch is the perfect choice for managing multiple PC's.

- Control up to 2 computers / servers with one set of console device
- USB keyboard / mouse emulation with 2 sets of detachable KVM cables
- Compliant with Windows and Linux
- High video quality: up to 2048 x 1536 VGA resolution
- Auto-scan and LED display for computer monitoring
- Keyboard status restored when switching between computers
- Computer selection by front panel push buttons, keyboard hot key commands or Windows-based client switching software*
- User definable hot key (Windows only)
- USB interface power method
- Plug & Play and hot-pluggable
- 2-year limited warranty

Specifications

Hardware

Connections

- 2 computers

USB Interface

- USB 1.1 compliant

KVM Cable

- 2 sets of 1.2 m (4 ft.) USB KVM cables

Cable Interface

- To KVM
 - 1 x VGA / SVGA HDB 15-pin (male)
- To Computer
 - 1 x USB (type A)
 - 1 x VGA / SVGA HDB 15-Pin (male)

PC Port Connectors

- 2 x VGA / SVGA HDB 15-pin (female)

Console Port Connectors

- 2 x USB Keyboard / Mouse: (type A)
- 1 x VGA / SVGA 15-pin HDB (female)

Computer Selection

- Face panel push buttons, keyboard hot key commands or Windows-based client switching software*

Supported OS

- Windows and Linux

Auto-Scan Interval

- 10 seconds

Keyboard State

- Save and restore

Power Type

- USB interface power

Dimensions

- 98 x 70 x 28 mm (3.86 x 2.76 x 1.1 in.)

Weight

- 99 g (3.4oz)

Temperature

- Operating: 0°C ~ 40°C (32°F ~104°F)
- Storage: -20°C ~ 60°C (-4°F ~140°F)

Humidity

- Max 90% (non-condensing)

Certifications

- CE, FCC

Package Contents

- TK-207K
- Quick Installation Guide
- 2 sets of USB KVM cables (2 x 1.2 m / 4 ft.)

*For optimal performance, we recommend using a wired keyboard and mouse. Please go to <http://www.trendnet.com/downloads> to download the client switching software.