



United Security Products, Inc.

AD-2000F

Fire Spec Auto Dialers

Voice/Pager Dialers

United Security Products Automatic Voice Dialers are a NEW GENERATION of Security Communications and Notification equipment for the Security Professional. Small, Compact and User Friendly. USP Dialers deliver the most advanced technology in the World today. Available in Models ranging from single to 4 alarm zones. USP Dialers deliver voice and numeric messages to landline phones or cell phones in any language up to 8 numbers



The AD-2000F dialer features busy-line and no-answer detection to ensure prompt transmission of up to 4 prerecorded messages delivered sequentially to as many as 8 standard telephones, cellular phones, voice and/or numeric pagers. Messages to both local and long-distance calls can be transmitted. When activated, the dialer instantly begins calling the numbers in sequence, delivering each message 1 to 3 times in a row, in accordance with the preselected number of dialing attempts.

The AD-2000F is extensively programmable, offering personalized customization to fulfill virtually any residential or business requirement. Plain-English prompts walk the user through the process in a timely manner.

Installation and hookup are quick and easy, whether installed in conjunction with normally open, normally closed dry contact or voltage activation sensors. The unit can also function as a stand-alone device, by simple connection to an ordinary telephone jack.

Applications

- Security/burglar/fire alarm notification
- Equipment malfunction notification
- Environmental warning notification
- High/Low Temperature threshold notification

Features

- A Full Featured Security System Ideal for fire alarm control panel notification requirements-24VDC Operation
- 4 Separate voice message alarm zones
- Calls up to 8 telephones, cell phones or pagers
- Built-In Line Seizure
- Remote Turn Off feature allows termination of activated channel
- EEPROM Memory retains programming despite power loss
- Listen-In verification and 2 way communication
- Universal Dial Tone. Works with any analog phone system.
- Built-In Auxiliary Output to drive external siren, strobe or relay
- NOTE: Power Supply Sold Separately

Specifications

Power source: 24 VDC

Current (OPERATE mode - standby): 28mA typical.

Current (OPERATE mode - dialing): 100mA max.

Activation:

1) N.C. Activation: dialer activates when an "open" is detected

2) N.O. Activation: dialer activates when a "close" is detected

3) Voltage Activation:

N.C. (applied voltage: Min. +5VDC, Max. +28VDC)

N.O. (loss of continuous voltage: Min. 0VDC, Max. 0.25VDC)

Max. Digits for outgoing numbers: 50

Operating temperature range: -18 to 55 C (0 to 130 F)

Dimensions (inches): 6x4x1.5in

Weight (ounces): 10 oz

Mounting: Wall or Flat Surface

Case Material: ABS

Color: White

Warranty: 1 Year

About USP

United Security Products, Inc. has supplied quality products to the security alarm industry for over 40 years, with proven performance in more than 100 million installations. Security systems dealers rely on USP for the most innovative products in the security industry. For your next installation, be sure to specify USP products.

40 Years of Superior American Manufacturing
Made in U.S.A
U.S. and FOREIGN PATENTS PENDING



United Security Products, Inc.

United Security Products • 13250 Gregg St. Suite B • Poway, CA 92064
Toll Free: 800-227-1592 • Tel: 858-413-0149 • Fax: 858-413-0124
www.unitedsecurity.com