

FEATURES:

- 24 VOLT DC "A" BATTERY POWER SUPPLY
- SIX OUTPUTS, 2 AMPS EACH
- REGULATED AND FILTERED
- FLOATING OUTPUT
- INPUT FUSE PROTECTED
- OUTPUT PROTECTED
- WALL MOUNT PLATE INCLUDED
- PROVIDES 240 VALCOM POWER UNITS



DESCRIPTION:

Wall mountable switching 24 Vdc, 12 Amp Filtered "A" talk battery power supply with six 2 Amp outputs, each protected with auto-reset poly switches.

Specifications:

INPUT

Voltage/Frequency 120 Vac, 47-63 Hz
Power 360 Watts
Protection 6.3A/120VAC Line Fuse
Connection IEC 320 Input + AC Cord

OUTPUT

Voltage 24 Vdc Regulated + 2%
Filtered, Floating
10 mV Ripple Maximum
Current 12 Amps, Six 2A/Outputs
Protection Six 2 A Auto-reset
Poly switches
Connections Wire Cage Connectors

REGULATORY

UL, cUL Listed
Class 2 Power Supply
FCC Class B

ENVIRONMENT

Temperature 32 - 104 °F (0 - 40 °C)
Humidity 10-95% Non-condensing

DIMENSIONS AND WEIGHT

12.1 "H x 8.7 "W x 3.9 "D (30.734 cm x 22.098 cm x 9.906 cm)
Weight: 7.7 lbs (3.465 kg)
Shipping Weight: 10.0 lbs (4.5 kg)

MOUNTING

Wall Mount
Mounting plate and hardware included

ARCHITECTS' AND ENGINEERS

The wall or rack mountable switching power supply, model number VP-12124 shall be -24 VDC power supply capable of providing 12 amperes of current. The design of this regulated power supply shall use switching technology, shall provide auto recovery short circuit protection and shall feature six (6) individual class "B" outputs each capable of providing 1/6 of the supply's rated current. Additionally, the supply's design shall incorporate EMI filtering, a minimum 80% efficiency, a 3 second power up delay, a working input frequency range of 47 to 63 Hertz and an LED status indicator. The supply shall also feature +/- 2 % voltage regulation and over voltage protection.

The supply shall be capable of operating within a temperature range of 0° to 50° C and a humidity range of 10% to 95% non-condensing.

Maximum dimensions of the supply shall not exceed 12.1 "H x 8.7 "W x 3.9 "D (30.734 cm x 22.098 cm x 9.906 cm). The weight shall be 7.7 lbs (3.465 kg).

LIMITED WARRANTY

Valcom, Inc. warrants its products to be free from defects in materials and workmanship under conditions of normal use and service for a period of one year from the date of shipment. The obligation under this warranty shall be limited to the re-placement, repair or refund of any such defective device within the warranty period, provided that:

1. inspection by Valcom, Inc. indicates the validity of the claim,
2. the defect is not the result of damage, misuse, or negligence after the original shipment,
3. the product has not been in any way repaired by others and that factory sealed units are unopened (A service charge plus parts and labor will be applied to units defaced or physically damaged).
4. freight charges for the return of products to Valcom, Inc. are prepaid,
5. all units "out of warranty" are subject to a service charge. The service charge will cover minor repairs (major repairs will be subject to additional charges for parts and labor)

This warranty is in lieu of and excludes all other warranties expressed or implied, and in no event shall Valcom, Inc. be liable for any anticipated profits, consequential damages, loss of time or other losses incurred by the buyer in connection with the purchase, operation or use of the product.

This warranty specifically excludes damage incurred in shipment. In the event a product is received in damaged condition, the carrier should be notified immediately. Claims for such damage should be filed with the carrier involved in accordance with the F.O.B. point.