

# ***ENVIROALERT®***



## TEMPERATURE PROBE FLAT CABLE SPLICE KIT

- Apply in freezer and cooler situations.
- Minimize door gasket impact.
- Cable clamps and splice connectors included.

## Specifications

Cable Length	5' (1.53 m) 4-conductor Flat 24 AWG Cable
4 Splice Connectors	24-18 AWG
4 Cable Clamps	1 x1 x .25" (25.4 x 25.4 x 6.35 mm)

## Accessory for

Probe Detection	Model Number	Range
Temp Ultra Low (White) Stainless Steel	TEMP-UL-S	-112° to 32° F (-80° to 0° C)
Temp Low (Blue) Stainless Steel	TEMP-L-S	-58° to 158° F (-50° to 70° C)
Temp Low (Blue) Waterproof	TEMP-L-W	-58° to 158° F (-50° to 70° C)
Temp High (Red) Stainless Steel	TEMP-H-S	32° to 300° F (0° to 150° C)
Temp High (Red) Waterproof	TEMP-H-W	32° to 221° F (0° to 105° C)

Temperature sensors sold separately.



Visit [www.winland.com](http://www.winland.com), call 800.635.4269 or email [techsupport@winland.com](mailto:techsupport@winland.com) to learn more.

