

## PowerBlade



- Innovative wire & cable stripping system
- SOG® knife blade with bevel edge
- Cryogenic heat treated blade increases strength to enable longer sharpness and chip resistance
- Manufactured from AUS 8 stainless steel
- Lightweight tool handle military-style Zytel plastic
- Liner Lock Blade Release System to keep knife securely locked while in-use position

CAT. NO.	DESCRIPTION	WEIGHT
PA6575	Powerblade	.35 lbs

## Keyhole/Jab Saw



- Integrated blade and handle design provides maximum strength
- Ergonomic handle with non-slip grip
- Hardened steel blade with clog-free teeth
- Pointed tip easily punches through drywall for plunge cuts
- Blade cuts on both push and pull strokes
- Hole in handle may be used for lanyard or convenient storage

CAT. NO.	UPC NO.	DESCRIPTION	WEIGHT
301A	23641	6" Keyhole Saw	.27 lbs

## Retractable Saw Set



- Cuts drywall, wood, conduit, metal, pvc and plastics
- 6" blade retracts into the handle for convenience and safety
- Accepts most 6" (or shorter) standard reciprocating saw blades and jab saw blades
- Ergonomically designed handle allows force to be applied both on the push and pull stroke
- Built-in blade storage area can hold 2 additional blades
- Adjustable blade can be used at any length or the 3 hard stops can be used for aggressive sawing
- Jab blade and a bi-metal blade included
- U S Patent #D527,602

CAT. NO.	UPC NO.	DESCRIPTION	WEIGHT
311	13110	Retractable Saw Set	.35 lbs
<b>R</b> 311-JAB	71945	Jab Blades	—

## 12" Heavy Duty Hack Saw



- Over-molded rugged design for heavy-duty use and comfort
- Fully-adjustable blade tension up to 30,000 psi for longer blade life and faster, accurate cuts
- Alternative 45° blade mounting allows for flush cutting
- Mounting for most reciprocating saw blades for extra versatility
- Handy blade storage in tubular frame
- Convenient front grip feature for two-handed sawing
- Complete with bi-metal blade (12"/24 TPI)
- Length is 15-3/4"
- Lifetime limited warranty

CAT. NO.	UPC NO.	DESCRIPTION	WEIGHT
333A	23635	12" Heavy Duty Hacksaw	2.15 lbs
<b>R</b> 333-1218	10037	12" (30.5 cm) Bi-metal Blades, 18 teeth per inch, 5 pack	—
<b>R</b> 333-1224	10038	12" (30.5 cm) Bi-metal Blades, 24 teeth per inch, 5 pack	—
<b>R</b> 333-1232	10039	12" (30.5 cm) Bi-metal Blades, 32 teeth per inch, 5 pack	—