



KRAMER

VIA GO

Wireless Presentation Solution

| HDMI | Ethernet - RJ-45



VIA GO gives iOS, Android, Chromebook, PC, and Mac users instant wireless connectivity with advanced presentation capabilities. The product features content streaming with crystal-clear mirrored images and stunning video playback and includes iOS, Windows and Android mirroring. VIA GO is easy and flexible to install with both built-in Wi-Fi and LAN connectivity and includes industry-leading 1024-bit encryption for secure use on the internal network

FEATURES

Wireless Device Connectivity - No dongle needed

60fps Streaming Multimedia - Share HD wireless video streaming (using the VIA app Multimedia feature). Supports up to 6Mbps video bit rate when using the built-in Wi-Fi module in Access Point mode

Easy to Use - Simple and intuitive user interface

Display Participants - Up to two participant screens can be displayed simultaneously on main screen

Graphic Output Formats - Outputs to either an HDMI or Mini DisplayPort display. Note: Does not support graphic output to both the HDMI and Mini Display Port simultaneously

iOS and Android Mirroring

Seamless Integration with VIA Site Management (VSM) Software & the VIA Pad

Wi-Fi Band Support - 2.4GHz (Access Point mode), 2.4GHz/5GHz (Client mode)

Warranty - 3-years on hardware, 1-year on software



KRAMER

TECHNICAL SPECIFICATIONS

I/O:	4 USB 3.0, 1 LAN on an RJ-45 connector
GRAPHIC OUTPUTS:	1 HDMI, 1 mini DisplayPort, support up to 1080p60 (using the VIA app Multimedia feature) / WUXGA resolution. Note: Does not support graphic output to both the HDMI and Mini Display Port simultaneously
AUDIO OUTPUT:	3.5mm mini jack for HP/speakers
PROCESSOR:	Intel® Braswell CPU, Dual Core 1.04GHz
MAIN MEMORY:	2GB, high-speed
STORAGE:	eMMC, 32GB
LAN:	Gigabit LAN
WIRELESS COMMUNICATION:	Intel dual-band wireless 802.11ac – model 3160NGW
AUDIO:	Analog or embedded HDMI
POWER SUPPLY:	45W power adapter (19V/2.37A)
PRODUCT DIMENSION:	11.70cm x 10.70cm x 3.00cm (4.61" x 4.21" x 1.18") W, D, H
PRODUCT WEIGHT:	0.5kg (1.1lbs) approx
SHIPPING DIMENSION:	23.20cm x 13.60cm x 10.00cm (9.13" x 5.35" x 3.94") W, D, H
SHIPPING WEIGHT:	1.0kg (2.1lbs) approx
INPUT VOLTAGE:	100V~220V AC, 50/60Hz, auto sensing
INCLUDED ACCESSORIES:	Power cord, Kramer mini-DP to VGA adapter, VESA mounting bracket

