

DS-2CD2T52-I5

5 MP EXIR Bullet Outdoor Network Camera

- Up to 5 MP High Resolution
- Electronic Shutter
- Dual Video Streams
- Digital Wide Dynamic Range
- 3D Digital Noise Reduction
- 3-Axis Adjustment
- 12 VDC and PoE
- IR Cut Filter with Auto Switch
- 165 ft (50 m) EXIR Range
- IP67 Weather-Resistant Protection
- Mobile Monitoring via Hik-Connect or iVMS-4500




Hikvision DS-2CD2T52-I5 EXIR Bullet Network Camera is an affordable solution for all of your security needs. It features a powerful 5 MP sensor that captures images with a resolution of 2560×1920 at up to 30 fps. The DS-2CD2T52-I5 EXIR Bullet Network Camera supports dual stream live view and is equipped with an IR lamp with a range of up to 165 ft (50 m), which facilitates nighttime recording.

Available model: DS-2CD2T52-I5



DS-2CD2T52-I5	
Camera	
Image Sensor	1/3" progressive scan CMOS
Minimum Illumination	0.014 lux @ <i>f</i> /1.4, AGC on, 0 lux with IR
Shutter Speed	1/3 s to 1/100,000 s
Lens	4 mm (6 mm option) @ <i>f</i> /1.4
Lens Mount	M12
Day/Night	IR cut filter with auto switch
DNR	3D DNR
Compression Standard	
Video Compression	H.264+/H.264/MJPEG
H.264 Type	Main profile
Video Bit Rate	256 Kbps to 16 Mbps
Dual Streams	Supported
Image	
Max. Resolution	2560 × 1920
Main Stream	60 Hz: 20 fps (2560 × 1920), 30 fps (2048 × 1536), 30 fps (1920 × 1080), 30 fps (1280 × 720)
Sub Stream	60 Hz: 30 fps (352 × 240, 640 × 360)
Others	Saturation, brightness, contrast adjustable by client software or web browser, mirror, BLC, ROI, dual stream, anti-flicker, privacy mask
Network	
Network Storage	NAS (supports NFS, SMB/CIFS), ANR
Detection	Intrusion detection, line crossing detection, motion detection, dynamic analysis
Alarm Trigger	Tampering alarm, HDD full, HDD error, network disconnected, IP address conflicted
Protocols	TCP/IP, UDP, ICMP, HTTP, HTTPS, FTP, DHCP, DNS, DDNS, RTP, RTSP, RTCP, PPPoE, NTP, UPnP, SMTP, SNMP, IGMP, 802.1X, QoS, IPv6, Bonjour
Standard	ONVIF (Profile S, Profile G), PSIA, CGI, ISAPI
General Function	Password protection, IP address filtering, anonymous access, watermark
Interface	
Communication Interface	1 RJ-45 10M/100M Ethernet port
Network	
Operating Conditions	-22° to 140° F (-30° to 60° C), humidity 95% or less (non-condensing)
Power Supply	12 VDC ±25%, PoE (802.3af Class 3)
Power Consumption	7.5 W maximum
IR Range	165 ft (50 m)
Protection Level	IP67
Dimensions	11.8" × 3.4" × 3.35" (299.71 mm × 86.48 mm × 85.11 mm)
Weight	2.6 lbs (1,200 g)

Dimensions



Accessories

			
CB130 Conduit Base	CBS Conduit Base	PM Pole Mount Adapter	CM Corner Mount Adapter