

TruVision™ camera matrix

| GE Part #                                                                                                | Description                                                                         | Resolution (TVL) | Lux | Voltage     | Accessories | Outputs |
|----------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------|-----|-------------|-------------|---------|
|  <b>TruVision™ Dome</b> |                                                                                     |                  |     |             |             |         |
| TVD-DOME-HR                                                                                              | TruVision Dome, 500 TVL Color, Varifocal Lens, 500 TVL, 2.6mm-6.0mm AI, 12VDC/24VAC | 500              | 0.2 | 12vdc/24vac | n/a         | BNC     |

| GE Part #                                                                                                  | Description                                                                                              | Resolution (TVL) | Lux         | Voltage | Accessories               | Outputs |
|------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|------------------|-------------|---------|---------------------------|---------|
|  <b>TruVision Dome IR</b> |                                                                                                          |                  |             |         |                           |         |
| TVD-TIR-SR                                                                                                 | TruVision IR Dome Camera 380 TVL Color, 4.3mm Fixed Lens, 10m IR Range, 12VDC only, IP67                 | 380              | 0.0 (IR ON) | 12vdc   | Mounting bracket supplied | BNC     |
| TVD-TIR-MR                                                                                                 | TruVision IR Dome Camera 480 TVL Color, 4.0mm - 9.0mm AI Varifocal Lens, 20m IR Range, 12VDC only, IP66  | 480              | 0.0 (IR ON) | 12vdc   | Mounting bracket supplied | BNC     |
| TVD-TIR-HR                                                                                                 | TruVision IR Dome Camera, 530 TVL Color, 3.5mm - 8.0mm AI Varifocal Lens, 20m IR Range, 12VDC only, IP66 | 530              | 0.0 (IR ON) | 12vdc   | Mounting bracket supplied | BNC     |

| GE Part #                                                                                                 | Description                                                                                                 | Resolution (TVL) | Lux         | Voltage     | Accessories               | Outputs |
|-----------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|------------------|-------------|-------------|---------------------------|---------|
|  <b>TruVision Cam IR</b> |                                                                                                             |                  |             |             |                           |         |
| TVC-BIR-SR                                                                                                | TruVision IR Bullet Camera 380 TVL Color, 4.3mm Fixed Lens, 10m IR Range, 12VDC only, IP67                  | 380              | 0.0 (IR ON) | 12vdc       | Mounting bracket supplied | BNC     |
| TVC-BIR-MR                                                                                                | TruVision Bullet IR Camera 480 TVL Color, 3.5mm - 12.0mm AI Varifocal Lens, 25m IR Range, 12VDC/24VAC, IP67 | 480              | 0.0 (IR ON) | 12vdc/24vac | Mounting bracket supplied | BNC     |
| TVC-BIR-HR                                                                                                | TruVision IR Bullet Camera 530 TVL Color, 6.0mm - 50.0mm AI Varifocal Lens, 55m IR Range, 12VDC/24VAC, IP67 | 530              | 0.0 (IR ON) | 12vdc/24vac | Mounting bracket supplied | BNC     |

| GE Part #                                                                                                    | Description                                                                                       | Resolution (TVL) | Lux | Voltage | Accessories | Outputs |
|--------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------|-----|---------|-------------|---------|
|  <b>TruVision™ Covert</b> |                                                                                                   |                  |     |         |             |         |
| TVC-SDC2-HR                                                                                                  | TruVision Covert Smoke Detector (Non-Functioning) 550 TVL Color, 0.4 lux, 2.8mm lens, 12VDC only  | 550              | 0.4 | 12vdc   | Included    | BNC     |
| TVC-SDC3-HR                                                                                                  | TruVision Covert Smoke Detector (Non-Functioning) 550 TVL Color, 0.4 lux, 3.8mm lens, 12VDC only  | 550              | 0.4 | 12vdc   | Included    | BNC     |
| TVC-PIR2-HR                                                                                                  | TruVision Covert Motion Detector (Non-Functioning) 550 TVL Color, 0.4 lux, 2.8mm lens, 12VDC only | 550              | 0.4 | 12vdc   | Included    | BNC     |
| TVC-PIR3-HR                                                                                                  | TruVision Covert Motion Detector (Non-Functioning) 550 TVL Color, 0.4 lux, 3.8mm lens, 12VDC only | 550              | 0.4 | 12vdc   | Included    | BNC     |

| GE Part #                                                                                                       | Description                                                                                               | Resolution (TVL) | Lux | Voltage | Accessories | Outputs |
|-----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|------------------|-----|---------|-------------|---------|
|  <b>TruVision™ Specialty</b> |                                                                                                           |                  |     |         |             |         |
| TVC-RCM-HR                                                                                                      | TruVision Specialty Rugged Corner Mount, 550 TVL Color, 0.4 lux, 2.8mm lens, 12VDC only, Vandal Resistant | 550              | 0.4 | 12vdc   | Included    | BNC     |

| GE Part #                                                                                                    | Description                                        | Resolution (TVL) | Lux | Voltage     | Accessories                                                               | Outputs |
|--------------------------------------------------------------------------------------------------------------|----------------------------------------------------|------------------|-----|-------------|---------------------------------------------------------------------------|---------|
|  <b>TruVision PTZ 16X</b> |                                                    |                  |     |             |                                                                           |         |
| GEC-DV-16SN                                                                                                  | TruVision PTZ 16X, Surface/Pendant Type IP66, NTSC | 480              | 1.0 | 24vac/24vdc | Wall mount kit<br>Pendant mount kit<br>Pipe mount adapter<br>TBAR support | BNC     |
| GEC-DV-16FN                                                                                                  | TruVision PTZ 16X, Flush Type, NTSC                | 480              | 1.0 | 24vac/24vdc | GEC-DV-WM, GEC-DV-PM,<br>GEC-DV-PMA, GEC-DV-TBAR                          | BNC     |

| GE Part #                                                                                                         | Description                                           | Resolution (TVL) | Lux                    | Voltage | Accessories                                                                                                       | Outputs |
|-------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|------------------|------------------------|---------|-------------------------------------------------------------------------------------------------------------------|---------|
|  <b>TruVision PTZ Mini 12X</b> |                                                       |                  |                        |         |                                                                                                                   |         |
| TVP-12C                                                                                                           | TruVision Mini PTZ, 12X Color, Indoor, NTSC           | 540              | 1.0                    | 24vac   | Wall mount kit<br>Pendant mount kit<br>Pipe mount adapter<br>TBAR support                                         | BNC     |
| TVP-12DN                                                                                                          | TruVision Mini PTZ, 12X Day/Night, Indoor, NTSC       | 540              | 1.0 (Color), 0.2 (B/W) | 24vac   | TVP-FM, TVP-ISB (smoke bubble), TVP-IWA (requires TVP-WM or TVP-LWM), TVP-WM, TVP-LWM<br>Ceiling bracket supplied | BNC     |
| TVP-12C-E                                                                                                         | TruVision Mini PTZ, 12X Color, Outdoor IP66, NTSC     | 540              | 1.0                    | 24vac   | TVP-WM, TVP-LWM, TVP-ESB (smoke bubble)                                                                           | BNC     |
| TVP-12DN-E                                                                                                        | TruVision Mini PTZ, 12X Day/Night, Outdoor IP66, NTSC | 540              | 1.0 (Color), 0.2 (B/W) | 24vac   | TVP-WM, TVP-LWM, TVP-ESB (smoke bubble)                                                                           | BNC     |

| GE Part #                                                                                                           | Description                                           | Resolution (TVL) | Lux     | Voltage     | Accessories                             | Outputs |
|---------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|------------------|---------|-------------|-----------------------------------------|---------|
|  <b>CamPlus™ IP Rugged Dome</b> |                                                       |                  |         |             |                                         |         |
| GEC-IPDRH-DN-POE                                                                                                    | CamPlus IP Rugged Dome, 520 TVL, MPEG-4, 24VAC, 12VDC | 520              | 0.5/0.1 | 24vac/12vdc | Flush mount<br>Wall mount<br>Pole mount | BNC     |

| GE Part #                                                                                                  | Description                                                                         | Resolution (TVL) | Lux  | Voltage                | Accessories         | Outputs |
|------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------|------|------------------------|---------------------|---------|
|  <b>MiniView Dome</b> |                                                                                     |                  |      |                        |                     |         |
| MD2-1500                                                                                                   | MiniView Dome, 2" Discreet, High-Res, Color w/24 VAC Adapter, 3-Axis, 480TVL, 12VDC | 480              | 1.00 | 12vdc (24 vac adapter) | Wall mount included | BNC     |