
RACKRAIL, 10-32, 43 RU, SLIM 5 SERIES

5AR43 |



FEATURES & BENEFITS

• Facilitates rear hanging of equipment • Permits panels to be “mid-mounted” • All brackets, rails and hardware included • Cable chase kit required when using this option with ganged enclosures • Works with steel side panels only; will not accommodate wood side panels



- Adjustable, split design allows for mid- and rear-hanging support
- Works with steel side panels; not compatible with wood side panels
- Cable chase kit is required when used with ganged racks
- Includes all necessary brackets, rails, and hardware

SPECIFICATIONS

GENERAL INFO

Finish: Black E-Coat

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

Greenguard: Yes

DIMENSIONS

Usable Height: 75.25

Depth (US): 2.625

Height (US): 72.94

Width (US): 0.675

Rack Units: 43

TECHNICAL INFORMATION

Rackrail Type: 10-32

Material: Steel