



BLANK PANEL, 4 RU, HINGED

AP-4 |

FEATURES & BENEFITS

The hinged access panel provides quick passage to rack interiors. Solid and vented panels available. Fabricated from easily machinable 13-gauge black powder coated aluminum, this access panel is perfect for those situations where access to the rear of connector panels is required. Captive 10-32 threaded thumbscrews require no tools to open and will not get lost.



- Solid panel controls airflow and accidental contact
- Aluminum construction is easily machinable
- Hinged on one side for easy interior access
- Captive 10-32 threaded thumbscrews require no tools to open

SPECIFICATIONS

GENERAL INFO

Finish: Black Powder Coat

ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

Greenguard: Yes

DIMENSIONS

Panel Width: 19

Depth (US): 1.4

Height (US): 7

Width (US): 19
Rack Units: 4

TECHNICAL INFORMATION

Material: Aluminum