

## BLANK PANEL, 6 RU, HINGED

AP-6 |



### FEATURES & BENEFITS

The hinged access panel provides quick passage to rack interiors. Solid and vented panels available. Fabricated from easily machinable 13-gauge black powder coated aluminum, this access panel is perfect for those situations where access to the rear of connector panels is required. Captive 10-32 threaded thumbscrews require no tools to open and will not get lost.



- Solid panel controls airflow and accidental contact
- Aluminum construction is easily machinable
- Hinged on one side for easy interior access
- Captive 10-32 threaded thumbscrews require no tools to open

### SPECIFICATIONS

#### GENERAL INFO

Finish: Black Powder Coat

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

Greenguard: Yes

#### DIMENSIONS

Panel Width: 19

Depth (US): 1.4

Height (US): 10.5

Width (US): 19  
Rack Units: 6

TECHNICAL INFORMATION

Material: Aluminum