
GOOSENECK LIGHT, 1 RU PANEL

LT-GN-PNL |



FEATURES & BENEFITS

These bright rack lights (187 Lumens*) allow for more rack visibility, and the flexible strong gooseneck lets you direct the light where it is needed most. The reliable, long lasting LEDs have a 20,000 hour bulb life, and these lights include an on/off button for instant control. Available as 120V adapter, or as a rackmount panel with dual gooseneck lights. (*Contact us for details.)



- Bright LEDs for high visibility
- 8 LEDs provide 187 lumens
- Long lasting, with expected 20,000 hour bulb life

SPECIFICATIONS

ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

Greenguard: Yes

DIMENSIONS

Depth (US): 5.06

Height (US): 1.75

Width (US): 19

Rack Units: 1

TECHNICAL INFORMATION

LightOutput 1FCD: 175 (331 total)