

PERIPHERALS

PTZ / Dome / Fisheye Camera Housings / Mounts

						
SHP-3701H	SHP-3701F	SHD-3000F1	SHD-3000F2	SHD-3000F3	SHD-3000F4	SBP-300HM1
Outdoor Housing for PTZ Dome - For outdoor applications - Weatherproof rated to IP66 - Aluminium + Polycarbonate - IK10 vandal resistant - Can be used with SNP-3300A/3301/3302/3350/3370/3371/3750/5200/5300/5320/5321/5430/6200/6201/6320/6321/L5233/L6233 SCP-2250/2251/2270/2271/2273/2330/2370/2371/2373/2430/3250/3370/3371/3430	In-Ceiling Housing for Dome - For indoor applications - Polycarbonate - Can be used with SNP-3300A/3301/3302/3350/3370/3371/3750/5200/5300/5320/5321/5430/6200/6201/6320/6321/L5233/L6233 SCP-2250/2251/2270/2271/2273/2330/2370/2371/2373/2430/3250/3370/3371/3430	In-Ceiling Housing for PTZ Dome - For indoor applications - Polycarbonate - Can be used with PNV-9080R SND-5083/5084/5084R/6083/6084/6084R/7084/7084R SNV-5084/5084R/6084/6084R/6085R/7084/7084R/8080/8081R SCD-6081R SCV-6081R	In Ceiling Housing for Dome - For indoor applications - Polycarbonate - Can be used with QND-6070R/7080R SND-6011R/L5083R/L6083R SCD-5080/5082/5083/5083R/6021/6083R SUD-5082	In Ceiling Housing for Dome - For indoor applications - Polycarbonate - Can be used with QNV-6070R/7080R SNV-L5083R/L6083R SCV-5082/5082R/5083/5083R/5085/6023R/6083R	In Ceiling Housing for Dome - For indoor applications - Polycarbonate - Can be used with PND-9080R	Hanging Mount - Aluminum - Can be used with SNP-3300A/3301/3302/3350/3370/3371/3750/5200/6200/3120 SCP-2250/2251/2430/3250/3430/2120/3120/2270/2330/2370/3370 SBP-300CM/300LM/300WM/300WM1
						
SBP-301HM2	SBP-301HM3	SBP-301HM4	SBP-300HM5	SBP-300HM6	SBP-300HM7	SBP-300HM8
Hanging Mount - Aluminum - Can be used with QNV-7080R/6070R SNV-L6083R/L5083R/1080R/1080 SND-7084R/7084/6084R/6084/6083/5084R/5084/5083 SCV-6083R/6023R/5085/5083R/5083/5082R/5082/3083/3082/3081/2082R/2081R/2081 SCD-6081R SBP-300CM/300LM/300WM/300WM1	Hanging Mount - Aluminum - Can be used with SNV-3080/3082/3120/5080/5080R/7080/7080R/7082 SNP-5300/5320/5321/5430/6201/6320/6321/L5233/L6233 SCV-2060/2080/3080/3120 SCP-2271/2273/2371/2373/3371 SBP-300CM/300LM/300WM/300WM1	Hanging Mount for 3M Fisheye Cameras - Aluminum - Can be used with SNF-7010/7010V/7010VM SBP-300CM/300LM/300WM/300WM1	Hanging Mount for 5M Fisheye Cameras - Aluminum - Can be used with SNF-8010/8010VM SBP-300CM/300LM/300WM/300WM1	Hanging Mount - Aluminum - Can be used with PNV-9080R SNV-5084/5084R/6084/6084R/6085R/7084/7084R/8080/8081R SCV-6081R SBP-300CM/300LM/300WM/300WM1	Hanging Mount - Aluminum - Can be used with QND-6010R/6020R/6030R/7010R/7020R/7030R SND-L5013/L6012/L6013/L6013R/L6014R SNV-6013 SCD-6023R SBP-300CM/300LM/300WM/300WM1	Hanging Mount - Aluminum - Can be used with PND-9080R SND-6084R/6084/6083/5084R/5084/5083 SCD-6081R SBP-300CM/300LM/300WM/300WM1
						
SBP-122HM	SBP-300HF	SBP-301HF	SBP-300TM/300TM1	SBP-300CM	SBP-300WM1/300WM	SBP-300LM
Hanging Mount - Aluminum - Can be used with QNV-6010R/6020R/6030R/7010R/7020R/7030R QND-6070R/7080R SCD-5080/5082/5083/5083R/6021/6083R SND-6011R/L5083R/L6083R SUD-5082 SBP-300CM/300LM/300WM/300WM1	Built-in SFP Install Base for PTZ Cameras - Aluminum - LC SFP port type 100Mbps Ethernet speed (Default speed : 1000Mbps) - IEEE 802.3u, IEEE 802.3z support - Audio input/output, 3.5mm type 24V AC, IP66, IK10, -50°C to +55°C - Can use with SNP-6320H/5430H	Built-in SFP Install Base for PTZ Cameras - Aluminum - LC SFP port type 100Mbps Ethernet speed (Default speed : 1000Mbps) - IEEE 802.3u, IEEE 802.3z support - Audio input/output, 3.5mm type 24V AC, IP66, IK10, -50°C to +55°C - Can use with SNP-6321H/L6233H/5321H/5321H	Wall Ceiling Mount for 3M/5M Fisheye Cameras - Poly carbonate - Can be used with SNF-7010VM/7010V/7010 (SBP-300TM) SNF-8010/8010VM (SBP-300TM1)	Ceiling Mount - Aluminum + SECC - Can be used with hanging mount and outdoor PTZ	Wall Mount - Aluminum + SECC - Can be used with hanging mount and outdoor PTZ	Parapet Mount - Aluminum + SECC - Can be used with hanging mount and outdoor PTZ