






















PERIPHERALS

PTZ / Dome / Fisheye Camera housings / Mounts

 <p>SHP-3701H</p>	 <p>SHP-3701F</p>	 <p>SHD-3000F1</p>	 <p>SHD-3000F2</p>	 <p>SHD-3000F3</p>	 <p>SHD-3000F4</p>	 <p>SBP-300HM1</p>
<p>Outdoor Housing for PTZ Dome</p> <ul style="list-style-type: none"> For outdoor applications Weatherproof rated to IP66 Aluminium + Polycarbonate IK10 vandal resistant Can be used with SNP-3300A/3301/3302/3350/3370/3371/ 3750/5200/5300/5320/5321/5430/ 6200/6201/6320/6321/L5233/L6233 SCP-2250/2251/2270/2271/2273/2330/ 2370/2371/2373/2430/3250/3370/ 3371/3430 	<p>In-Ceiling Housing for Dome</p> <ul style="list-style-type: none"> For indoor applications Polycarbonate Can be used with SNP-3300A/3301/3302/3350/3370/3371/ 3750/5200/5300/5320/5321/5430/ 6200/6201/6320/6321/L5233/L6233 SCP-2250/2251/2270/2271/2273/2330/ 2370/2371/2373/2430/3250/3370/ 3371/3430 	<p>In-Ceiling Housing for PTZ Dome</p> <ul style="list-style-type: none"> For indoor applications Polycarbonate Can be used with PNV-9080R SND-5083/5084/5084R/6083/ 6084/6084R/7084/7084R SNV-5084/5084R/6084/6084R/6085R/ 7084/7084R/8080/8081R SCD-6081R SCV-6081R 	<p>In Ceiling Housing for Dome</p> <ul style="list-style-type: none"> For indoor applications Polycarbonate Can be used with QND-6070R/7080R SND-6011R/L5083R/L6083R SCD-5080/5082/5083/ 5083R/6021/6083R SUD-5082 	<p>In Ceiling Housing for Dome</p> <ul style="list-style-type: none"> For indoor applications Polycarbonate Can be used with QNV-6070R/7080R SNV-L5083R/L6083R SCV-5082/5082R/5083/ 5083R/5085/6023R/ 6083R 	<p>In Ceiling Housing for Dome</p> <ul style="list-style-type: none"> For indoor applications Polycarbonate Can be used with PND-9080R 	<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with SNP-3300A/3301/3302/3350/3370/ 3371/3750/5200/6200/3120 SCP-2250/2251/2430/3250/3430/ 2120/3120/2270/2330/2370/3370 SBP-300CM/300LM/300WM/300WM1
 <p>SBP-301HM2</p>	 <p>SBP-301HM3</p>	 <p>SBP-301HM4</p>	 <p>SBP-300HM5</p>	 <p>SBP-300HM6</p>	 <p>SBP-300HM7</p>	 <p>SBP-300HM8</p>
<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with QNV-7080R/6070R SNV-L6083R/L5083R/1080R/1080 SND-7084R/7084/6084R/6084/6083/ 5084R/5084/5083 SCV-6083R/6023R/5085/5083R/5083/ 5082R/5082/3083/3082/3081/ 2082R/2081R/2081 SCD-6081R SBP-300CM/300LM/300WM/300WM1 	<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with SNV-3080/3082/3120/5080/5080R/ 7080/7080R/7082 SNP-5300/5320/5321/5430/6201/ 6320/6321/L5233/L6233 SCV-2060/2080/3080/3120 SCP-2271/2273/2371/2373/3371 SBP-300CM/300LM/300WM/300WM1 	<p>Hanging Mount for 3M Fisheye Cameras</p> <ul style="list-style-type: none"> Aluminum Can be used with SNF-7010/7010V/7010VM SBP-300CM/300LM/300WM/300WM1 	<p>Hanging Mount for 5M Fisheye Cameras</p> <ul style="list-style-type: none"> Aluminum Can be used with SNF-8010/8010VM SBP-300CM/300LM/300WM/300WM1 	<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with PNV-9080R SNV-5084/5084R/6084/6084R/6085R/ 7084/7084R/8080/8081R SCV-6081R SBP-300CM/300LM/300WM/300WM1 	<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with QND-6010R/6020R/6030R/ 7010R/7020R/7030R SND-L5013/L6012/L6013/L6013R/ L6014R SNV-6013 SCD-6023R SBP-300CM/300LM/300WM/300WM1 	<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with PND-9080R SND-6084R/6084/6083/ 5084R/5084/5083 SCD-6081R SBP-300CM/300LM/300WM/300WM1
 <p>SBP-122HM</p>	 <p>SBP-300HF</p>	 <p>SBP-301HF</p>	 <p>SBP-300TM/300TM1</p>	 <p>SBP-300CM</p>	 <p>SBP-300WM1/300WM</p>	 <p>SBP-300LM</p>
<p>Hanging Mount</p> <ul style="list-style-type: none"> Aluminum Can be used with QNV-6010R/6020R/6030R/ 7010R/7020R/7030R QND-6070R/7080R SCD-5080/5082/5083/5083R/6021/6083R SND-6011R/L5083R/L6083R SUD-5082 SBP-300CM/300LM/300WM/300WM1 	<p>Built-in SFP Install Base for PTZ Cameras</p> <ul style="list-style-type: none"> Aluminum LC SFP port type 100Mbps Ethernet speed (Default speed : 1000Mbps) IEEE 802.3u, IEEE 802.3z support Audio input/output, 3.5mm type 24V AC, IP66, IK10, -50°C to +55°C Can use with SNP-6320H/5430H 	<p>Built-in SFP Install Base for PTZ Cameras</p> <ul style="list-style-type: none"> Aluminum LC SFP port type 100Mbps Ethernet speed (Default speed : 1000Mbps) IEEE 802.3u, IEEE 802.3z support Audio input/output, 3.5mm type 24V AC, IP66, IK10, -50°C to +55°C Can use with SNP-6321H/L6233H/ 5321H/5321H 	<p>Wall Ceiling Mount for 3M/5M Fisheye Cameras</p> <ul style="list-style-type: none"> Poly carbonate Can be used with SNF-7010VM/7010V/7010 (SBP-300TM) SNF-8010/8010VM (SBP-300TM1) 	<p>Ceiling Mount</p> <ul style="list-style-type: none"> Aluminum + SECC Can be used with hanging mount and outdoor PTZ 	<p>Wall Mount</p> <ul style="list-style-type: none"> Aluminum + SECC Can be used with hanging mount and outdoor PTZ 	<p>Parapet Mount</p> <ul style="list-style-type: none"> Aluminum + SECC Can be used with hanging mount and outdoor PTZ