

PTZ Mounts

Built-in SFP Install Base for PTZ Cameras



	SBP-300HF	SBP-301HF
COMPATIBLE MODEL		
Camera List	SNP-6320H/5430H	SNP-6321H/5321H
EXTERNAL CONNECTION		
Alarm I/O	Input 4ea / Output 2ea	
Remote Control Interface	RS-485/422	
Audio	Input / Output, 3.5mm type	
CVBS	BNC type, For installation	
Power Line	24V AC, 2-wire	
OPTICAL CHARACTERISTICS		
Support SFP Voltage	3.3V typical	
Support SFP Current	Max. 300mA	
Support SFP Cage	Standard mini-SFP cage (For 6.5mm pitch SFP)	
Support SFP Port Type	LC type	
Required SFP Speed	1250Mbps (For 1000Mbps ethernet), 155Mbps (For 100Mbps ethernet)	
Required SFP's BER (Bit Error Rate)	Max. 10 ⁻¹²	
Transmission Method (Optical)	Mode depends on SFP module	
Optical Mode (Long / Short Wave)	Mode depends on SFP module	
Cable Insertion Loss (dB)	Mode depends on SFP module	
NETWORK CHARACTERISTICS		
RJ-45 : Ethernet Speed	100Mbps	
RJ-45 : Ethernet Physical Layer	100 Base-T	
RJ-45 : Ethernet Standard	IEEE 802.3u support	
Speed Transition (100 ↔ 1000Mbps)	External Dip switch	
Fiber : Default Speed	1000Mbps	
Fiber : Ethernet Speed	100Mbps, 1000Mbps	
Fiber : Ethernet Physical Layer	100 Base-FX, 1000 Base-X	
Fiber : Ethernet Standard	IEEE 802.3u, IEEE 802.3z support	
NETWORK CHARACTERISTICS		
Operating Temperature / Humidity	-50°C ~ +50°C (-58°F ~ 122°F) / Less than 90% RH	
Ingress Protection	IP66	
Vandal Resistance	IK10	
ELECTRICAL		
Power Consumption	Max. 65W, 3.1A (Heater on)	
Input Voltage / Current	24V AC	
MECHANICAL		
Color / Material	Ivory / Aluminum	
Dimension (WxH)	Ø163.9 x 157.9mm (Ø6.45" x 6.22"), Ø163.9 x 187.9mm (Ø6.45" x 6.7") (With NPT-Coupling)	
Weight	1.1Kg (2.43 lb), 1.4Kg (3.09 lb) (With NPT-Coupling)	

* The latest product information / specification can be found at www.samsungsecurity.com

Dimensions

Unit : mm (inch)

