



760207274 | CPP-UDDM-M-1U-24

**Discrete Distribution Module Panel, – 1U**

## Product Classification

Portfolio	CommScope®
Product Type	Copper patch panel
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Depth	119.38 mm   4.70 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

## Electrical Specifications

ANSI/TIA Category	5e   6   6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Brand	CommScope®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

## Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

