

## TEMP°ALERT®



### Mechanical Temperature Monitor with Dual High and Low Output

- Connects to any hard wire or wireless alarm system.
- Separate output for high and low alarm signals.
- Sleek, low-profile styling.
- Normally open (N.O.)
- Do not put console in freezer/cooler. Use an EnviroAlert with a wired sensor.

## Specifications

Power Requirements	No power required to operate
Low Limit Adjust Range	30° to 90° F (-1° to 32.2° C) Non-condensing environment
High Limit Adjust Range	40° to 100° F (4° to 37.7° C) Non-condensing environment
Minimum Temp Span	10° Recommended distance between high and low set points
Temp Accuracy	±3° F (±1.7° C)
Temp Response Time	TC = 14 minutes
Outputs	Gold plated N.O. dry contacts. Not for high voltage use.
Contact Output Rating	12VDC @ 50mA
Weight	6 oz (0.17 kg)
Dimensions	4.5 x 3.25 x 1" (11.4 x 8.3 x 2.5 cm)
Mounting	Surface mount



Visit [www.winland.com](http://www.winland.com), call 800.635.4269 or email [info@winland.com](mailto:info@winland.com) to learn more.

