George Risk Industries

(800) 523-1227

Home

Products

About GRI

Contact GRI

Where to Buy

Testimonials

What's New!

100 Series Miniature Surface Mount Switch Sets



100-12

Lifetime Warranty

• UL and ULC approved

Adhesive and screw mount

Standard 12" leads or screw terminals

Available in closed loop, open loop and SPDT

• Standard gap up to 1"

• Wide gap up to 1 1/4"

• Longer Leads, zip cord or jacketed cable upon request

• Built-in E.O.L. resistors and diodes upon request

Switches or magnets available separately

Private labeling available on request



110-12



100-T




The 100 Series come with mounting screws. Both the 100 and 110 are furnished with adhesive tape for proper mounting on aluminum or vinyl. Spacers, covers, switch only, magnet only and additional adhesive tape are also available separately.




110-T



100-TC





MINIATURE SURFACE MOUNT SWITCH SET



100/110 SERIES (1) (1)

- Miniature Profile Makes This Series Ideal For Residential and Light Commercial Applications
 - ◆ Surface Mount Magnetic Contact
- ◆ Screw Down Flange or Self Stick ◆ 12" #22AWG Leads or Screw Terminals
 - ◆ Longer Leads, Zip Cord or Jacketed Cable Upon Request
 - ◆ Hermetically Sealed ◆ Plated Contacts Resist Sticking or Freezing
 - ◆ Covers and Mounting Hardware Included
 - ◆ Built-in E.O.L. Resistors and Diodes Upon Request
 - ◆ Supervisory Loops Upon Request
 - Switches and Magnets Available Separately
 - ◆ Colors: White, Brown, Gray, Almond ◆ Lifetime Warranty
 - ◆ Private Labeling Upon Request











100-12

100-T

100-TC

110-12

110-T

PART NUMBERS:			
	Closed Loop	Open Loop	SPDT
Standard Gap Up To 1"	100-12	101-12	102-12
	100-T	101-T	
	100-TC	101-TC	
	110-12	111-12	112-12
	110-T	111-T	
Wide Gap Up To 1 1/4"	100-12WG	101-12WG	102-12WG
	100-TWG	101-TWG	
	100-TCWG	101-TCWG	
	110-12WG	111-12WG	112-12WG
	110-TWG	111-TWG	

WARRANTY:

Lifetime warranty against workmanship, material and factory defects.

GEORGE RISK INDUSTRIES, INC. GR.I. PLAZA KIMBALL, NE 69145



TOLL-FREE 1-800-445-5218 TOLL-FREE 1-800-523-1227 (308) 235-4645 FAX (308) 235-3561


E-MAIL: grisales@megavision.com WEB SITE: www.grisk.com



MINIATURE SURFACE MOUNT SWITCH SET

INSTALLATION APPLICATIONS:

The G.R.I. 100 style switch is one of our most popular miniature surface mount switches. Available in both flanged: 100-12; and without flanges: 110-12; this low profile series is perfect for residential and commercial use where a larger configuration is not appropriate. Available in regular and wide gap, the set incorporates into most decor requirements without being noticeable. The 100-12 comes with mounting screws. Both the 100 and the 110 are furnished with 3M adhesive tape for proper mounting on aluminium, wood or vinyl. Spacers, switch only, magnet only and additional 3M adhesive tape are also available separately. Order P/N 100-TC if molded covers are desired.



GRI products meet or exceed these minimum general specifications:

PART	LOOP	ELECTRICAL	REED	MAXIMUM	MAXIMUM	MAXIMUM	MAXIMUM
NUMBER	TYPE	CONFIG.	FORM	MAXIMUM INITIAL CONTACT RESISTANCE	CONTACT RATING	SWITCHING VOLTAGE	SWITCHING CURRENT
				(Ω)	(W)	(VDC)	(A)
100-12	Closed	N/O	А	.150	10	200	.500
100-12WG	Closed	N/O	Α	.150	10	200	.500
100-T	Closed	N/O	Α	.150	10	160	.400
100-TWG	Closed	N/O	Α	.150	10	160	.400
100-TC	Closed	N/O	Α	.150	10	160	.400
100-TCWG	Closed	N/O	Α	.150	10	160	.400
110-12	Closed	N/O	Α	.150	10	200	.500
110-12WG	Closed	N/O	Α	.150	10	200	.500
110-T	Closed	N/O	Α	.150	10	160	.400
110-TWG	Closed	N/O	Α	.150	10	160	.400
101-12	Open	N/C	В	.140	5	175VDC	.250
101-12WG	Open	N/C	В	.140	5	175VDC	.250
101-T	Open	N/C	В	.140	5	175VDC	.250
101-TC	Open	N/C	В	.140	5	175VDC	.250
101-TCWG	Open	N/C	В	.140	5	175VDC	.250
101-TWG	Open	N/C	В	.140	5	175VDC	.250
111-12	Open	N/C	В	.140	5	175VDC	.250
111-12WG	Open	N/C	В	.140	5	175VDC	.250
111-T	Open	N/C	В	.140	5	175VDC	.250
111-TWG	Open	N/C	В	.140	5	175VDC	.250
102-12	Open/Closed	SPDT	С	.140	5	175VDC	.250
102-12WG	Open/Closed	SPDT	С	.140	5	175VDC	.250
112-12	Open/Closed	SPDT	С	.140	5	175VDC	.250
112-12WG	Open/Closed	SPDT	С	.140	5	175VDC	.250

CONTACT YOUR G.R.I. DISTRIBUTOR OR CALL:

GEORGE RISK INDUSTRIES, INC. GR.I. PLAZA KIMBALL, NE 69145



TOLL-FREE 1-800-445-5218 TOLL-FREE 1-800-523-1227

(308) 235-4645 FAX (308) 235-3561

E-MAIL: grisales@megavision.com WEB SITE: www.grisk.com