

06 DX Format Supervised Wireless

DXT-21 2-Button, 1-Channel Handheld Transmitter

• ORDER # SNT00376



DXT-23 3-Button, 4-Channel Handheld Transmitter

• ORDER # SNT00377

DXT-25 5-Button, 8-Channel Handheld Transmitter

• ORDER # SNT00378

Features:

- Unique "Extra" top button
- High visibility operate LED
- Two type 2032 lithium batteries supplied
- Pocket/belt clip supplied
- DX format
- RF frequency: 315 MHz
- 1.6" W x 4.2" H x 0.8" D

NOTE:

DX format transmitters are supervised for low-battery reporting only. Hourly status reports are not sent from DX format transmitters.

DXT-601 1-Button, 1-Channel Key Ring Transmitter

• ORDER # SNT00410



Features:

- Two type 2016 lithium batteries supplied
- Detachable key ring supplied
- DX format
- RF frequency: 315 MHz
- 1.25" W x 2.25" H x 0.48" D

DXT-54 Passive Infrared Motion Detector Transmitter

• ORDER # SBT00013



Features:

- Alarm and low-battery transmissions
- Walk-test mode
- Fresnel lens with 24 facets
- Battery saver circuitry
- 9-Volt alkaline battery supplied
- DX format
- RF frequency: 315 MHz
- 3.2" W x 4.4" H x 1.75" D

DXT-31 Door/Window Sensor

• ORDER # SBT00014



Features:

- Alarm, alarm restore, and low-battery transmissions
- Includes magnet for internal contact
- Includes mounting shoe
- External contact terminals
- DX format
- N/O or N/C input loop circuit
- Powered by two 2032 lithium batteries (included)
- RF frequency: 315 MHz
- 1.6" W x 3.4" H x 1.2" D

DXT-61A 1-Button, 1-Channel Pendant Transmitter

• ORDER # SNT00380A



Features:

- Famous "Panic Button" design
- 30-Inch neck chain included
- Test/operate LED
- Type GP-23 12-volt alkaline battery supplied
- DX format
- RF frequency: 315 MHz
- 1.42" W x 2.2" H x 0.66" D

DXT-81 Bill Trap Transmitter

• ORDER # SNT00383



Features:

- Low-battery reporting only when cash drawer is open
- Alarm, restore, test transmissions
- Lithium battery-powered
- Test LED
- Transmit repeat feature ensures reliability
- DX format
- RF frequency: 315 MHz
- 2.4" W x 4.5" H x 0.8" D

DXT-41 1-Channel, 1-Button Key Ring Transmitter

• ORDER # SNT00381



DXT-42 3-Channel, 2-Button Key Ring Transmitter

• ORDER # SNT00382

Features:

- Two type 1620 lithium batteries supplied
- Detachable key ring supplied
- DX format
- RF frequency: 315 MHz
- 1.25" W x 2.25" H x 0.48" D

32 Compatibility Charts

RECEIVERS AND CONTROL PANELS

TRANSMITTERS	RECEIVERS					CONTROL PANELS		RECEIVERS AND CONTROL PANELS											
	D-67 (ALL)	DX-12	D-2R	D-4R	D-8C	DXR-701	DXR-702	DXSR-1504	DXSR-1508	DVS-1200	DVS-2400	DUAL-824	PERS-2400B	PERS-3600B	AL-1	SXR-64A	XR-1	XR-4	XR-16
D-21A	●	●	●	●	●														
D-22A	●	●	●	●	●														
D-22B, C, D	●	●	●	●	●														
D-23R	●	●	●	●	●														
D-24A	●	●	●	●	●														
D-4B	●	●	●	●	●														
ET-1B	●	●	●	●	●														
ET-2-12 or -19	●	●	●	●	●														
DXT-21						●	●	●	●	●	●	●	●	●	●	●			
DXT-23						●	●	●	●	●	●	●	●	●	●	●			
DXT-25						●	●	●	●	●	●	●	●	●	●	●			
DXT-31						●	●	●	●	●	●	●	●	●	●	●			
DXT-41						●	●	●	●	●	●	●	●	●	●	●			
DXT-42						●	●	●	●	●	●	●	●	●	●	●			
DXT-54						●	●	●	●	●	●	●	●	●	●	●			
DXT-61A						●	●	●	●	●	●	●	●	●	●	●			
DXT-81						●	●	●	●	●	●	●	●	●	●	●			
DXT-601						●	●	●	●	●	●	●	●	●	●	●			
DXS-10										●	●	●							
DXS-21						●	●	●	●	●	●	●	●	●	●	●			
DXS-23								●	●	●	●	●	●	●	●	●			
DXS-25								●	●	●	●	●	●	●	●	●			
DXS-31						●	●	●	●	●	●	●	●	●	●	●			
DXS-32						●	●	●	●	●	●	●	●	●	●	●			
DXS-54						●	●	●	●	●	●	●	●	●	●	●			
DXS-62						●	●	●	●	●	●	●	●	●	●	●			
DXS-64						●	●	●	●	●	●	●	●	●	●	●			
DXS-73							●	●	●	●	●	●	●	●	●	●			
DXS-80							●	●	●	●	●	●	●	●	●	●			
DXS-81							●	●	●	●	●	●	●	●	●	●			
DXS-91							●	●	●	●	●	●	●	●	●	●			
LMT-1/303																●			
ST-23A																●			
T-90D																●			
TGB-96																●			
TMD-90																●			
TX-91,-92,-94																●			
XT-1																	●	●	●
XT-1H																	●	●	●
XT-2H																	●	●	●
XT-4																	●	●	●
XT-4H																	●	●	●

■ = preferred product choice