

**UC1DDD2-0C | UNC5-GY****Uniprise Category 5e U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Gray Jacket****OBSOLETE****This product was discontinued on: March 31, 2017****Replaced By**CO155D2-0C
CO5E-U-CM-GY

Category 5e U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Gray Jacket

Ordering Details

Complete Part Number	Complete Description Code	Cord Length
UC1DDD2-0CF005	UNC5-GY-5FT	5 ft
UC1DDD2-0CF007	UNC5-GY-7FT	7 ft
UC1DDD2-0CF010	UNC5-GY-10FT	10 ft

Product Classification

Portfolio	Uniprise®
Product Type	Twisted pair patch cord
Regional Availability	North America

Dimensions

Cord Length, maximum	100 ft 30 m
Cord Length, minimum	1 ft 1 m

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Gray
Brand	Uniprise®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

UC1DDD2-0C | UNC5-GY

Package Quantity 1
Pairs, quantity 4

Mechanical Specifications

Conductor Type Stranded
Material Type Copper alloy | Polycarbonate
Outlet/Module Contact Plating Precious metals
Plug Insertion Life, minimum 750 times
Plug Retention Force, minimum 133 N | 30 lbf
Wiring T568B

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

CC4656044/BU | 5EJ4/UNC5 GRAY BULK REEL (Product Component—not orderable) — Datapipe® 5EJ4 Category 5e U/UTP Cable, non-plenum, gray jacket, 4 pair count, bulk length, reel