



HORIZONTAL RK, 4U PIVOT, 5U FIXED, 36" D, PUTTY

VWM-4-5-36K-PW |

FEATURES & BENEFITS

With a low-profile, patent-pending design, this pre-configured VWM Series Wall Cabinet is ideal for mounting patch panels, hubs, routers, and switches within two mounting bays or 9 total rackspaces. It includes everything needed for a simple solution, but also can support additional customization in Lever Lock™ small device mounting within the cabinet and/or on the door, thermal management, cable management and power distribution for a complete system that ensures uptime and reliability on the wall.



PRODUCT
ENVIRONMENTAL PROFILE

- Two mounting areas for a total of 9 rackspaces
- 4 RUs in upper bay with pivoting rackrail for patch panels
- 5 RUs in the lower bay with fixed rackrail for switches and routers
- Rackrail features both 10-32 thread and cage nut
- Flexible position spaces to mount the rackrail where it's needed
- Solid door that restricts user access and visibility for additional security
- Laser knockouts on the top, bottom and sides for cable entry and thermal management
- Integral electrical box simplifies power distribution
- Finished in a durable putty colored powder coat

SPECIFICATIONS

GENERAL INFO

Finish: Putty Powder Coat
UL Standards Tested: UL 2416

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
Greenguard: Yes
CSA Listing Info: 60950-1
CSA Listed: Yes

UL Listing No: E313734

DIMENSIONS

Usable Depth: 27.8 with J-Box

Capacity Weight (US): 150

Depth (US): 12

Height (US): 36

Width (US): 25

Rack Units: 4 pivot and 5 fixed

TECHNICAL INFORMATION

Rackrail Type: 10-32 and cage nut

UL Load Capacity: 150

Material: Steel