



# KRAMER

## VIA Connect PLUS

Simultaneous Wired and Wireless  
Presentation and Collaboration Solution

| HDMI | Ethernet - RJ-45



VIA Connect PLUS provides simultaneous wired and wireless presentation and collaboration in multiple huddle spaces with no need for any additional hardware. This cost-effective solution includes all the benefits of VIA Connect PRO together with an HDMI input. With any laptop or mobile device, meeting participants can display or stream full uninterrupted HD video (up to 1080p60), images and documents, or share any size file. The whiteboard feature lets you annotate, sketch out ideas or edit shared documents on the main display from your device.

VIA Connect PLUS features mirroring for iOS (MacBook, iPad and iPhone), Lollipop OS 5.0 or newer (Android), and Chromebook. You can show up to four user screens on a single main display

## FEATURES

**HDMI Wired Input** - Enables hardwiring your computer or other HDMI compatible device such as a camera, multimedia player or computer

**60fps Streaming Multimedia** - Share HD wireless video streaming (using the VIA app Multimedia feature)

**Wireless Connection for up to 254 Devices** - Utilizing Compatible External Wireless Network  
iOS and Android Mirroring

**Wireless Device Connectivity** - No dongle needed

**DHCP Support**

**Graphic Output Formats** - Outputs to either an HDMI or Mini DisplayPort display. Note: Does not support graphic output to both the HDMI and Mini Display Port simultaneously

**CloudBased File Sharing** - Drag and drop files to the internal VIA cloud storage (32GB)

**Whiteboard Support**

**Control** - Give a participant control over a presenter's PC for true collaboration

**Chat** - Send an instant message to another user

**iCloud Integration**

**Seamless Integration with VIA Site Management (VSM) Software & the VIA Pad**

**Multilingual Support** - Experience VIA in your language

**Warranty** - 3years on hardware



# KRAMER

## TECHNICAL SPECIFICATIONS

---

INPUTS:	4 USB 3.0, 1 LAN on an RJ45 connector, 1 HDMI
GRAPHIC OUTPUTS:	1 HDMI, 1 mini DisplayPort. Note: Does not support graphic output to both the HDMI and Mini Display Port simultaneously
AUDIO OUTPUT:	1 S/PDIF
Max. Resolution	for the HDMI Input: 1080p@60Hz
PROCESSOR:	4th generation Intel® Dual core 1.4GHz
MAIN MEMORY:	4GB, high speed
STORAGE:	32GB, solidstate drive
LAN:	Gigabit LAN
AUDIO:	Analog or embedded HDMI, S/PDIF Realtek ALC269
POWER SUPPLY:	65W power adapter (19V, 3.4A)
INPUT VOLTAGE:	100V~220V AC, 50/60Hz, auto sensing
PRODUCT DIMENSION:	11.80cm x 11.50cm x 4.00cm (4.65" x 4.53" x 1.57" ) W, D, H
PRODUCT WEIGHT:	0.5kg (1.1lbs) approx
SHIPPING DIMENSION:	23.20cm x 13.60cm x 10.00cm (9.13" x 5.35" x 3.94" ) W, D, H
SHIPPING WEIGHT:	1.0kg (2.2lbs) approx
INCLUDED ACCESSORIES:	Power cord, Kramer HDMI Male to Female cable extender, VESA mounting bracket



# KRAMER

## CONFIGURATIONS

VIA Digital Signage  
Module

License for Dynamic Content Display Feature

