

1-1671373-1

Fiber adapter plate, 1U, unpopulated, for holding up to 4 Quick-Fit modules

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber adapter plate
Regional Availability	Australia/New Zealand EMEA

Body Features

Color	Black
-------	-------

Configuration Features

Number of Ports	0
-----------------	---

Dimensions

Depth	39.70 mm 1.56 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Industry Standards

Standards Compliance	UL 94 V-0
----------------------	-----------

Usage Conditions

Operating Temperature	-10 – 60 °C 14 – 140 °F
Relative Humidity (Operating)	5 – 95 %
Relative Humidity (Storage)	5 – 95 %
Storage Temperature	-40 – 158 °F -40 – 70 °C

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant