



1-2111375-0 | TMRJ-1SUPB-SH010M

**MRJ21™ High Speed Cable Assembly, 180° MRJ21 to Plug, 1GbE, 24-pair, CMR, 10 m, blue**

- Universal modular copper cabling platform for applications such as Gigabit Ethernet, VoIP and Power over Ethernet
- Increased I/O port density and cleaner cabling schemes compared to RJ45 connectors and cabling
- Robust die cast cable covers provide straight, or 45 deg left/right cable exit for ease of routing

## Product Classification

Portfolio	CommScope®
Brand	MRJ21™
Product Series	MRJ21
Product Type	Copper trunk cable assembly
Regional Availability	Latin America   North America

## Dimensions

Cord Length	10 m
Diameter Over Jacket	12 mm

## Electrical Specifications

ANSI/TIA Category	6
Safety Voltage Rating	150 V

## Environmental Specifications

Environmental Space	Plenum
Flammability Rating	CM
Safety Standard	cUL

## General Specifications

Construction Type	Stranded
Interface, connector A	MRJ21 plug
Interface, connector B	RJ45 plug
Application	Ethernet, 1 GbE
Cable Type	F/UTP (shielded)
Interface Feature, connector A	Backshell, 180°
Interface Feature, connector B	Booted
Jacket Color	Blue
Package Quantity	1
Pairs, quantity	24
Total Ports, quantity	6

## Mechanical Specifications

1-2111375-0 | TMRJ-1SUPB-SH010M

Conductor Gauge, solid	24 AWG
Conductor Material	Bare copper
Conductor Type	Solid

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant