



1375187-2

SL110 Series Modular Jack, RJ45, 8-position, category 6, T568A/T568B, unshielded, with dust cover, black

Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	Modular jack
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Body Features

110 Block Material	Polycarbonate
Cover Color	Transparent
Cover Material	Polycarbonate

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm

Dimensions

Insulated Conductor Outside Diameter	0.057 in 1.45 mm
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

Housing Features

Housing Color	Black
Housing Material	Polycarbonate

Industry Standards

Standards Compliance	UL 94 V-0
----------------------	-----------

1375187-2

Packaging Features

Included	Strain relief
Packaging Method	Poly Bag
Packaging Quantity	1

Product Type Features

Performance Category	Category 6
Shielded	No
Applies To	Panel
Connector Type	Connector Assembly
Dust Cover	With
Jack Type	RJ45

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant