

**1499925-4****SL110 Series Modular Jack, RJ45, category 6, HD, unshielded, without dust cover, gray**

Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	Modular jack
Regional Availability	Asia Latin America North America

Body Features

110 Block Material	Polycarbonate
Inverted Jack Face	Yes

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm

Dimensions

Insulated Conductor Outside Diameter	0.057 in 1.45 mm
Solid Wire Range	.51 mm ² .65 mm ²
Stranded Wire Range	.14 mm ² .2 mm ²
Wire Range	22 AWG 24 AWG 26 AWG

Housing Features

Housing Color	Gray
Housing Material	Polycarbonate

Industry Standards

Standards Compliance	UL 94 V-0
----------------------	-----------

Mechanical Attachment

1499925-4

Mounting Type	SL Series Faceplate
---------------	---------------------

Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

Product Type Features

Performance Category	Category 6
Shielded	No
Applies To	Panel
Cable Type	Unshielded Twisted Pair
Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ45

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant